

VGA Coax Monitor Cable, Plenum-Rated High Resolution cable with RGB coax (HD15 M/M), 50-ft.

MODEL NUMBER: **P502-050-P**



Description

Tripp Lite's 50ft Plenum Rated SVGA cable is ideal in Educational or Commercial installations where local fire codes call for a CMP rated cable to run through walls, ceilings, and plenum air chambers. 100ft distance is achieved through high quality construction: 75ohm Coaxial conductors for Red, Green, and Blue (RGB) signals, each protected by a 93% tinned copper braid shield. An overall shield of Mylar foil and 85% Copper Braid shield ensures maximum signal integrity.

Features

- Superior molded cables with foil and braid shielding for maximum EMI/RFI protection
- UL Listed, CMP Rated Cable Jacket
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 male molded connectors
- Resolutions up to 2048 x 1536

Specifications

OVERVIEW	
Chromebook Compatible	No
Style	Monitor Cables
Model Type	VGA
Cable Types	MONITOR
INPUT	
Cable Length (ft.)	50

Highlights

- UL Listed, CMP rated cable
- Molded Ends with Gold-plated connectors
- 75Ohm Coax RGB conductors
- Resolutions up to 2048 x 1536

Applications

- Educational or Commercial locations where Fire Codes dictate the use of Plenum Rated cables. Ideal for schools with suspended ceiling mount projectors, or retail locations with Plasma screen displays.

Package Includes

- 50-ft. Plenum Rated SVGA/VGA Monitor Cable HD15M to HD15M Gold Connectors w/ RGB Coax



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	15.24
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	HD15 (MALE)
Connector B	HD15 (MALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.