



## 1880ENA1/NSC-12

12 PAIR - INDOOR BET - 110/110 - NO COVER

### Product Specifications


### UL497 Primary Protector for Communication Circuits

NAFTA Country of Origin: CANADA - All Models are "Buy America Act" Approved.

These 16 AWG steel building entrance terminals feature an industry standard 110 - style connector for both the input and output terminals. Also included are multiple external and internal ground lugs. UL approved standard on all terminals. Standard 5-pin protection modules, available in gas tube, solid state and hybrid versions, can be purchased separately. Call for more detailed information on RDUP/RUS-listed units.

## Features & Benefits

- 16 AWG Powder Coated Steel Construction
- Equipped with an Internal 26 AWG Fuse Link
- External Ground Connectors Accept 6 - 14 AWG Wire
- Industry Standard 5 Pin Design
- Exceeds UL497 Primary Protection Standards
- 110 Connector Accepts 22 - 26 AWG Wire



1880ENA1/NSC-12

### Ordering Information

Model Number	Stock Code	Pair Count	Input	Output	Dimensions (H" x W" x D")	Weight (lbs)
1880ENA1/NSC-12	307007	12	110	110	9.85 x 4.00 x 2.21	2.5

### 1880ENA1/NSC-12


12 PAIR - INDOOR BET - 110/110 - NO COVER



### Physical Dimensions

### UL497 Primary Protector for Communication Circuits

9.85 x 4.00 x 2.21  
(H" x W" x D")



### Notes

Installation:

Indoor Wall Mount