


14.4kW 3-Phase Switched PDU, 208V Outlets (6-C13 & 12-C19), Hubbell 50A CS8365C, 6ft Cord, 0U Vertical

MODEL NUMBER: **PDU3VSR6H50A**



Description

Tripp Lite 3 phase Switched PDU / Power Distribution Unit offers advanced network control and monitoring with the ability to turn on, turn off, recycle or lock-out power to each individual receptacle, monitor site electrical conditions and remotely monitor output power consumption per-phase or per-receptacle. PowerAlert interface supports remote control and custom notification of user-specified conditions via email, secure web, SNMP, Telnet or SSH interface. Individually switched outlets can be controlled in real-time to remotely reboot unresponsive network hardware, or be custom programmed for user-defined power-up and power-down sequences to ensure proper startup of interdependent IT systems and prevent inrush-related overloads as network equipment is first energized. Unused PDU outlets can be electronically locked off to prevent the connection of unauthorized hardware. Built-in local digital display and remote web/network interface reports detailed voltage, amperage and kilowatt output values per outlet, per breaker bank and per phase with additional reporting options for power unbalance percentage, IP address and sensor based temperature and humidity data (requires ENVIROSENSE sensor).

Features

- 14.4kW 3 phase 208V Switched Power Distribution Unit / PDU with built-in web/network interface
- Attached Hubbell CS8365C 50A (3P+E) 208V 3 phase input; 6 ft. / 1.8m cord
- 0U, 70 inch / 178cm vertical form factor
- 18 switched 208V outlets (6 C13, 12 C19) in 6 separately breakered 20A single phase load banks
- Supports power-on, power-off or reboot of each outlet on a real-time or programmable basis
- Enables reboot of locked equipment, custom power-on/power-off sequences, load-shedding of optional loads and disabling unused outlets
- Network interface provides PDU control and data regarding input voltage and per-phase load levels with +/-1% billing-grade accuracy
- Built-in local digital display and remote web/network interface reports detailed voltage, amperage and kilowatt output values per outlet, per breaker bank and per phase with additional reporting options for power unbalance percentage, IP address and sensor based temperature and humidity data (requires ENVIROSENSE sensor)

Highlights

- Switched 14.4kW 3 Phase 208V PDU; 70 in. / 178cm 0U vertical rackmount
- Reports voltage, frequency & load per-outlet or phase via ethernet interface
- 1% billing-grade accuracy, Multi-function digital display, Environmental monitoring options
- Hubbell CS8365C 50A 208V 3 phase input (3P+E); 6 ft. / 1.8m line cord
- 6 C13 & 12 C19 single phase switched outlets with Plug-lock cable retention inserts
- Temperature, humidity and contact closure monitoring options

Applications

- Ideal for 3 phase network configurations in datacenters and heavily configured equipment racks

Package Includes

- Switched rackmount PDU with pre-installed mounting buttons
- 6 C13/C14 and 12 C19/C20 Plug-lock inserts
- Spare installation buttons (2 9mm / 4 6mm)
- Rack mounting brackets
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- In-rack environmental reporting with optional ENVIROSENSE temperature / humidity sensor and rack access notification with up to 4 optional SRSWITCH door sensors
- Local display supports electronic 180 degree display rotation for overhead or under-floor input cable orientation
- Supports user-specified alarm notification thresholds
- DHCP/Manual configuration support
- 10/100 Mbps auto-sensing
- Real-time clock backup maintains the time of day and date even if the PDU is unpowered
- Tiered access privileges allow an administrator and a guest to login via web browser
- Alert notifications via email or SNMP traps offer immediate event notification
- Firmware upgrade ability supports future product enhancements
- Supports HTTP, HTTPS, PowerAlert Network Management System, SMTP, SNMPv1, SNMPv2, SNMPv3, Telnet, SSH, FTP, DHCP, BOOTP, NTP protocols
- Fully compatible with FREE PowerAlert Network Management System / NMS Software
- Included set of Plug-lock inserts keep C14 and C20 power cords solidly connected to PDU outlets
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications (set of 2 9mm buttons pre-installed, 2 9mm and 4 6mm spare buttons included)
- TAA Compliant Version Available - Order Tripp Lite PDU3VSR6H50ATAA

Specifications

OVERVIEW	
Style	Vertical rackmount
PDU Type	Switched
OUTPUT	
Output Capacity Details	14.4kW total capacity; 23.1A max per output phase; 20A max per breakered load bank; 16A max per C19 outlet; 12A max per C13 outlet; Phase L1-L2 feeds load banks 1&4; Phase L2-L3 feeds load banks 2&5; Phase L3-L1 feeds load banks 3&6
Frequency Compatibility	60 Hz
Output Receptacles	(6) C13; (12) C19
Output Nominal Voltage	208V single phase
Overload Protection	6 20A double-pole circuit breakers (2 per output phase)
Outlet Type	IEC-C13, IEC-C19
Customized Load Management Receptacles	Each outlet is individually controllable via remote interface
INPUT	
PDU Input Voltage	208
Maximum Input Amps	40
PDU Plug Type	HUBBELL CS8365C 50A
Input Cord Length (ft.)	6



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Input Cord Length (m)	1.8
Input Phase	3-Phase
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LEDs	Built-in digital display reports output amps, watts, unbalanced load percentage, temperature, humidity and IP address self-identification
Switches	Pushbutton scroll switch enables local power consumption display of each phase separately, output current, load level, unbalanced load percentage, temperature, humidity, display rotate and display IP address functions
PHYSICAL	
Shipping Dimensions (hwd / in.)	75.9 x 9.7 x 7.1
Shipping Dimensions (hwd / cm)	191.5 x 24.6 x 18
Shipping Weight (lbs.)	26.7
Shipping Weight (kg)	12.1
Unit Dimensions (hwd / in.)	70 x 2.17 x 2.49
Unit Dimensions (hwd / cm)	177.8 x 5.5 x 6.3
Unit Weight (lbs.)	20.6
Unit Weight (kg)	9.4
Material of Construction	Steel
Form Factors Supported	Vertical rackmount installation supported with included mounting brackets; supports toolless mounting in button-mount compatible racks
PDU Form Factor	Vertical (0U)
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
Storage Elevation (m)	0 to 3000m (0 to 10,000 ft.)
COMMUNICATIONS	
SNMP Compatibility	Yes, pre-installed SNMPWEBCARD provides remote monitoring via web, telnet, SSH and SNMP management systems
CERTIFICATIONS	
TAA Compliant Option	TAA Compliant Version Available - Order Tripp Lite PDU3VSR6H50ATAA
Certifications	Tested to UL 60950-1 (USA, Canada), Class A (Emissions), NOM (Mexico), RoHS compliant
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	2-year limited warranty
-------------------------------------	-------------------------

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.