


# 11.5kW 3-Phase Metered PDU, 240V Outlets (36-C13 & 9-C19), L22-20P, 415V input, 6ft Cord, 0U Vertical

MODEL NUMBER: PDU3XMV6L2220



### Highlights

- Metered 11.5kW 3-Phase 415V input 240V output PDU
- Set of 3 digital meters report output load level per phase in amps
- 70in / 1778mm 0U vertical format, toolless button-mount installation
- NEMA L22-20P 3 phase input; 6ft 1.8m line cord
- 36 C13 & 9 C19 single phase outlets; Included cord retention brackets

### Applications

Ideal for 3-phase network configurations in datacenters and heavily configured equipment racks.

### Package Includes

- Metered rackmount PDU with pre-installed mounting buttons
- Cord retention brackets
- Spare installation buttons (2 9mm / 4 6mm)
- Rack mounting brackets
- Owner's manual

### Description

Tripp Lite 3-phase Metered PDU / Power Distribution Units offer real-time local reporting of current levels in amps via set of 3 built-in digital meters. Enables visual monitoring of PDU current levels to preserve proper loading balance and prevent circuit overloads as additional equipment is added. Offers reliable rackmount multi-outlet power distribution from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

### Features

- 11.5 kW Metered Power Distribution Unit (PDU)
- 415V input with NEMA L22-20P 3-phase input connection
- 240V output with 36 C13 & 9 C19 single phase output receptacles
- 0U / 1778mm vertical rackmount installation supported
- Outlets are arranged in 3 metered 15 outlet load banks
- Included cord retention brackets keep vital network equipment plugged in and continuously powered
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications (set of 2 9mm buttons pre-installed, 2 9mm and 4 6mm spare buttons included)
- TAA Compliant Version Available - Order Tripp Lite PDU3XMV6L222TAA

## Specifications

OVERVIEW	
Style	Vertical rackmount
PDU Type	Metered



<b>OUTPUT</b>	
Output Capacity Details	11.5kVA (415V), 11kVA (400V), 10.5kVA (380V); 16A maximum output per phase
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(36) C13; (9) C19
Output Nominal Voltage	Single phase 240V (415V), 230V (400V), 220V (380V)
Outlet Type	IEC-C13, IEC-C19
<b>INPUT</b>	
PDU Input Voltage	415
Maximum Input Amps	16
PDU Plug Type	NEMA L22-20P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.8
Input Phase	3-Phase
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	5.6 x 6.8 x 76.8
Shipping Dimensions (hwd / cm)	14.2 x 17.3 x 195.1
Shipping Weight (lbs.)	13.8
Shipping Weight (kg)	6.3
Unit Dimensions (hwd / in.)	70 x 2.2 x 1.93
Unit Dimensions (hwd / cm)	177.8 x 5.6 x 4.9
Unit Weight (lbs.)	8
Unit Weight (kg)	3.6
Material of Construction	Steel
Form Factors Supported	Vertical rackmount installation supported with included mounting brackets; supports toolless mounting in button-mount compatible racks
PDU Form Factor	Vertical (0U)
<b>ENVIRONMENTAL</b>	
Relative Humidity	0-95% non-condensing
Operating Elevation (m)	0 to 3000m (0 to 10,000 ft.)
<b>CERTIFICATIONS</b>	
TAA Compliant Option	TAA Compliant Version Available - Order Tripp Lite PDU3XMV6L222TAA
Certifications	Tested to UL (USA), CSA (Canada), NOM (Mexico), CE (EU), Class A (Emissions), RoHS (Hazardous Substances)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.