



Building Entrance Terminals

HIGH SPEED DATA - INDOOR - 66 BLOCK SERIES - BET



2612QC/QCe

12 PAIR - CAT5e - INDOOR BET - 66/66 - NO COVER

Product Specifications


UL497 Primary Protector for Communication Circuits

NAFTA Country of Origin: CANADA - All Models are "Buy America Act" Approved.

The Enhanced Series is built to be a universal protector with throughput of up to 1Gbps and clamping speeds of 2-3 nanoseconds. Available in 66 block, 110 connector or BIX. Select the right voltage and protect everything from VOIP to networks, digital phones to VDSL2.

Features & Benefits

- Certified Category 5e
- 16 AWG Powder Coated Steel Construction
- Equipped with an Internal 26 AWG Fuse Link
- External Ground Connectors Accept 6 - 14 AWG Wire
- Industry Standard 5 Pin Design
- Exceeds UL497 Primary Protection Standards
- 66 Block Accepts 22 - 26 AWG Wire/18 - 19 AWG Stripped Solid Copper Wire



2612QC/QCe

Ordering Information

Model Number	Stock Code	Pair Count	Input	Output	Dimensions (H" x W" x D")	Weight (lbs)
2612QC/QCe	124114	12	66	66	9.85 x 4.00 x 2.69	2.5



Building Entrance Terminals

HIGH SPEED DATA - INDOOR - 66 BLOCK SERIES - BET




2612QC/QCe

12 PAIR - CAT5e - INDOOR BET - 66/66 - NO COVER

Physical Dimensions

UL497 Primary Protector for Communication Circuits

9.85 x 4.00 x 2.69
(H" x W" x D")



Notes

Installation: Indoor Wall Mount

When used in conjunction with the Circa Telecom CAT5e/Hybrid Module Series