

## 5.8kW Single-Phase Switched PDU, 208/240V Outlets (16 C13), L6-30P Input, 12ft Cord, 2U Rack-Mount

MODEL NUMBER: **PDUMH30HVNET**



### Description

Tripp Lite single phase Switched PDU / Power Distribution Unit offers advanced network control and monitoring with the ability to turn on, turn off, recycle or lock-out power to each individual receptacle, monitor site electrical conditions and remotely monitor output power consumption. PowerAlert interface supports remote control and custom notification of user-specified conditions via email, secure web, SNMP, Telnet or SSH interface.

Individually switched outlets can be controlled in real-time to remotely reboot unresponsive network hardware, or be custom programmed for user-defined power-up and power-down sequences to ensure proper startup of interdependent IT systems and prevent inrush-related overloads as network equipment is first energized. Unused PDU outlets can be electronically locked off to prevent the connection of unauthorized hardware. PDU output current consumption in amps is continuously displayed locally via visual meter and remotely via web/network interface to warn of potential overloads before critical IT mains or branch breakers trip.

### Features

- 30A 208/240V Switched Power Distribution Unit / PDU with built-in web/network interface (Agency derated to 24A continuous)
- Attached L6-30P 208/240V single phase input, 12 ft. / 3.6m input cord
- 2U horizontal rackmount form factor
- 16 switched c13 outlets
- Supports power-on, power-off or reboot of each outlet on a real-time or programmable basis
- Enables reboot of locked equipment, custom power-on/power-off sequences, load-shedding of optional loads and disabling unused outlets
- Network interface provides PDU control and data regarding input voltage and total output load level in amps
- Digital display continuously reports output load in amps in 3 segments (load bank 1, load bank 2, total)
- Supports user-specified alarm notification thresholds
- In-rack environmental reporting with optional ENVIROSENSE temperature / humidity sensor and rack access notification with up to 4 optional SRSWITCH door sensors
- DHCP/Manual configuration support
- 10/100 Mbps auto-sensing

### Highlights

- Switched 30A 208/240V PDU, 2U horizontal rackmount format
- Reports voltage, frequency & load level via ethernet interface
- Visual current meter, Reversible housing
- NEMA L6-30P input plug with attached 12 ft. / 3.6m line cord
- 16 switched C13 outlets with cord retention brackets
- Temperature, humidity and contact closure monitoring options

### Applications

- Ideal for network configurations requiring a switched, metered and monitored PDU supporting individual outlet rebooting, load shedding and remote web/network current monitoring of critical networking components

### Package Includes

- Rackmount PDU
- Installable 2U mounting brackets



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

- Real-time clock backup maintains the time of day and date even if the PDU is unpowered
- Tiered access privileges allow an administrator and a guest to login via web browser
- Alert notifications via email or SNMP traps offer immediate event notification
- Firmware upgrade ability supports future product enhancements
- Supports HTTP, HTTPS, PowerAlert Network Management System, SMTP, SNMPv1, SNMPv2, SNMPv3, Telnet, SSH, FTP, DHCP, BOOTP, NTP protocols
- Fully compatible with FREE PowerAlert Network Management System / NMS Software
- 2U horizontal rack installation supported in 2 or 4 post racks with included mounting brackets
- Mounting brackets support wall-mount and under-counter installation in many applications
- Included cord retention brackets
- TAA Compliant Version Available - Order Tripp Lite PDUMH30HVNETAA

## Specifications

OVERVIEW	
Style	Rackmount
PDU Type	Switched
OUTPUT	
Output Capacity Details	5kW (208V), 5.8kW (240V), 4.8kW (200V); 30A maximum (agency de-rated to 24A continuous)
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(16) C13
Output Nominal Voltage	200-240V nominal, single phase
Overload Protection	2 15A breakers protect 8 outlets each
Outlet Type	IEC-C13
Customized Load Management Receptacles	Each outlet is individually controllable via remote interface
INPUT	
PDU Input Voltage	200; 208; 240
Recommended Electrical Service	30A 208/240V
Maximum Input Amps	30
Maximum Input Amps Details	Agency de-rated to 24A continuous
PDU Plug Type	NEMA L6-30P
Input Cord Length (ft.)	12
Input Cord Length (m)	3.6
Input Phase	Single-Phase
USER INTERFACE, ALERTS & CONTROLS	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Front Panel LCD Display	Digital display reports output amps in 3 separately metered loading segments (BANK 1: Outlets #1-8; BANK 2: Outlets #9-16; BANK 3: All outlets combined)
Front Panel LEDs	16 power availability LEDs confirm power off/on status for each built-in outlet; Two additional LEDs identify which bank the visual current meter is reporting (Bank 1, Bank 2 or Banks 1&2 combined)
Switches	Pushbutton near the digital current meter advances the display of output current for Bank 1, Bank 2 and Banks 1&2 combined
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	8 x 20.5 x 17
Shipping Dimensions (hwd / cm)	20.3 x 113 x 80.6
Shipping Weight (lbs.)	17.1
Shipping Weight (kg)	7.8
Unit Dimensions (hwd / in.)	3.5 x 17.5 x 12.5
Unit Dimensions (hwd / cm)	8.9 x 44.5 x 31.75
Unit Weight (lbs.)	13.8
Unit Weight (kg)	6.3
Material of Construction	Metal
Form Factors Supported	2U rackmount. Includes mounting accessories for 4 post installation, requires optional <a href="#">2POSTRMKITWM</a> for 2 post rackmount installation)
PDU Form Factor	Horizontal (1U, 2U, etc)
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5-95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
<b>COMMUNICATIONS</b>	
SNMP Compatibility	Yes, pre-installed <a href="#">SNMPWEBCARD</a> provides remote monitoring via web, telnet, and SNMP management systems. Remote management gives user ability to turn connected loads on or off individually
<b>CERTIFICATIONS</b>	
TAA Compliant Option	TAA Compliant Version Available - Order Tripp Lite PDUMH30HVNETAA
Certifications	Tested to UL 60950-1 (USA, Canada), Class A (Emissions), NOM (Mexico), RoHS compliant
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	2-year limited warranty
-------------------------------------	-------------------------

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.