



**SNK Terminal Blocks**  
**T&B Catalog Number:**

1SNK505210R0000

**UPC Number:**

80432548814

**Status:**

Active

**Description:**

Gray, double deck feed through terminal block with 5.2 mm spacing, 20 Amp rated UL current with screw clamp connection and 2 feed through circuits

**Features**

Easy and ergonomic mounting thanks to the unique profile

Marking surfaces can be read clearly from any angle in an enclosure and are larger than standard markers

One unique end section and circuit separator fits all feed-through terminal blocks, reducing the use of accessories

**Application**

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

**General**

Style	Double Deck Feed Through
Color	Gray
Series	ZS4-D2
Connection Technology	Screw Clamp
UL Wire Range (AWG)	24-12

**Dimension Information**

Spacing (mm)	5.2
Spacing (Inches)	0.205

**Specifications**

UL Current (Amps)	20
UL Voltage (VAC)	300
IEC Voltage (VAC)	800
IEC Current (Amps)	29

**Packaging**

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	400
T&B Sold in UOM	Each
T&B Weight Per UOM	2.5 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com