

6-Outlet Commercial-Grade Surge Protector, 6-ft. Cord, 900 Joules, 12.5-in. length

MODEL NUMBER: **PM6SN1**



Highlights

- 6 outlets/6 ft. cord
- 900 joule rating

Applications

- Offers multiple outlet power distribution and surge suppression in workbench, wallmount or floor mount applications. Ideal protection for home appliances, entertainment centers, industrial equipment and other electronic loads.

Package Includes

- PM6SN1 Power Strip
- Warranty information
- Instruction manual

Description

The Waber-by-Tripp Lite PM6SN1 Power Strip offers a convenient method of power distribution and surge suppression in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R output receptacles, 6 foot AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Protects connected equipment from transient surges and line noise with built in surge suppression rated at 900 joules. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features metal housing, lighted power switch with integrated 15 amp resettable circuit breaker and attractive beige housing with black output receptacles and power cord.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip with surge suppression

SUPPRESSION - 900 joules AC suppression

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1449 3rd Edition (USA/400V rating), UL1363 (USA), cUL (Canada)
- 15 amp power handling capacity
- 6 foot AC line cord

Specifications

OVERVIEW



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|--|
| Style | Strip |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (6) 5-15R |
| Output (Watts) | 1800 |
| Circuit Breaker (amps) | 15 |
| USB Charging | No |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input Connection Type | NEMA 5-15P input plug |
| Input Cord Length (ft.) | 6 |
| Input Cord Length (m) | 1.8 |
| Input Cord Gauge Type | 14 gauge, SJT |
| Voltage Compatibility (VAC) | 120 |
| Maximum Surge Amps | 45000 |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | Combination AC circuit breaker and lighted two position power switch controls power to all outlets |
| Diagnostic LEDs | Protection present (green) |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 900 |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| UL1449 Let Through Rating | 400V - UL Verified |
| EMI / RFI Filtering | Up to 20dB |
| Immunity | Conforms to IEE 587 / ANSI C62.41 |
| DATALINE SURGE SUPPRESSION | |
| Telephone/DSL Protection | No |
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | No |
| PHYSICAL | |
| Shipping Weight (lbs.) | 1.5 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|--|
| Shipping Weight (kg) | 0.7 |
| Unit Dimensions (hwd / in.) | 12.5 x 2.5 x 1.5 |
| Unit Dimensions (hwd / cm) | 31.75 x 6.35 x 3.8 |
| Unit Weight (lbs.) | 1.25 |
| Unit Weight (kg) | 0.6 |
| Material of Construction | Metal |
| Integrated Keyhole Mounting Tabs | Keyhole mounting tabs enable wall mounting |
| Receptacle Color | Black |
| Color (AC Line Cord) | Black |
| Outlets Measurement (Center to Center) | 38.89mm |
| Keyhole Slot Mounting Measurement (Center to Center) | 165mm |
| SPECIAL FEATURES | |
| Right-Angle Plug | No |
| CERTIFICATIONS | |
| UL1449 3rd Edition (AC Suppression) | UL1449 3rd Edition |
| UL1363 (Power Tap) | UL1363 |
| cUL / CSA (Canada) | cUL |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.