



**SNK Terminal Blocks**  
**T&B Catalog Number:**

1SNK508010R0000

**UPC Number:**

80432548907

**Status:**

Active

**Description:**

Gray, feed through terminal block with 8 mm spacing, 57 Amp rated UL current and screw clamp connection

**Features**

Save space by connecting conductors up to 6 AWG in just 0.315 inch spacing

Easy and ergonomic mounting thanks to the unique profile

Marking surfaces can be read clearly from any angle in an enclosure and are larger than standard markers

One unique end section and circuit separator fits all feed-through terminal blocks, reducing the use of accessories

**Application**

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

**General**

Style	Feed Through
Color	Gray
Series	ZS10
Connection Technology	Screw Clamp

**Dimension Information**

Spacing (mm)	8
L x W x H (in)	2.09 x 0.315 x 1.92
Spacing (inches)	0.315

**Specifications**

UL Current (Amps)	57
UL Voltage (VAC)	1000
CSA Voltage (VAC)	600
CSA Current (Amps)	42

**Packaging**

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	600
T&B Sold in UOM	Each
T&B Weight Per UOM	3.5 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321

