



## SNK Terminal Blocks

### T&B Catalog Number:

1SNK516010R0000

**UPC Number:**

80432548931

**Status:**

Active

**Description:**

Gray feed through closed terminal block with 16 mm spacing, 150 amp rated UL current and screw clamp connection

### Features

Easy and ergonomic mounting thanks to the unique profile

Marking surfaces can be read clearly from any angle in an enclosure and are larger than standard markers

One unique end section and circuit separator fits all feed-through terminal blocks, reducing the use of accessories

### Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

### General

Style	Feed Through
Color	Gray
Mounting	DIN 3
Series	ZS35
Connection Technology	Screw Clamp

### Dimension Information

L x W x H (mm)	59 x 16 x 55.8
Spacing (mm)	16
L x W x H (in)	2.32 x .630 x 2.19
Spacing (inches)	0.630

### Specifications

UL Current (Amps)	150
UL Voltage (VAC)	600

### Packaging

T&B Order Multiple	20
T&B Inner Pack	20
Package in Units	80
T&B Sold in UOM	Each
T&B Weight Per UOM	12.38 lbs. per 100

### Certifications

Approvals	USR, CSA, CE
-----------	--------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321

