

MILAN managed switch

MIL-SM4004TG

(4) port 10/100/1000BASE-T + (4) 100/1000 SFP ports



The MIL-SM4004TG series of layer 2 managed switches provide high performance non-blocking switching. The switch has 4 auto-sensing 10/100/1000BASE-TX RJ-45 ports and 4 dual speed 100/1000 SFP ports.

Management features include port based, dynamic and static VLANs, GVRP, VLAN tagging, IGMP Snooping or querying, port mirroring, port security. Security includes static addressing, filtering and blocking of packets to identified MAC addresses. Four priority queues insure minimum delay for voice over IP or multimedia network data. Non-blocking 16 Gbps architecture assures rapid packet delivery while 8,000 MAC address table provides swift lookup and packet forwarding.

Additional Features

- ▶ IGMP query and snooping
- ▶ 802.1X Authentication
- ▶ Port Mirroring
- ▶ 8K MAC Address
- ▶ Telnet/Web-based management
- ▶ TFTP firmware upgrade
- ▶ Enable/disable ports
- ▶ Auto-Negotiation
- ▶ Forced modes, 10H/10H/100H/100F/1000F
- ▶ Auto-MDIX on all ports
- ▶ 802.3X Flow control
- ▶ Back-pressure
- ▶ X-Ring Support
- ▶ 1 Mbps Buffer
- ▶ Broadcast storm filter
- ▶ DHCP Client, Relay, Server
- ▶ SNMP and SMTP support
- ▶ MAC Address Security
- ▶ Bandwidth Allocation
- ▶ QoS port-based/Tag based, IPv4, Tos/IPv4, IPv6, DiffServ
- ▶ Ingress & Egress MAC address filter & static source MAC address lock

(4) 10/100/1000 Base-T ports + (4) SFP 1000BASE-X ports

- ▶ 4-port 10/100/1000BASE-T
- ▶ (4) 100/1000 SFP Ports
- ▶ Auto MDI/MDI-X
- ▶ Non-blocking switching architecture
- ▶ IEEE 802.1q VLAN tagging GVRP/MVR
- ▶ IEEE 802.1p Class of Service 4 priority queues

Specifications

Standards	IEEE Std. 802.3 10BASE-T; IEEE Std. 802.3u 100BASE-TX; IEEE Std. 802.3z Gigabit fiber; IEEE Std. 802.3ab 1000BASE-T; IEEE Std. 802.3x Flow control and Back-pressure; IEEE Std. 802.3ad Port trunk with LACP; IEEE Std. 802.1d Spanning Tree Protocol; IEEE Std. 802.1w Rapid spanning tree; IEEE Std. 802.1p Class of service IEEE Std. 802.1q VLAN Tagging IEEE Std. 802.1x User Authentication
Protocols	CSMA/CD
Technology	Store and Forward switching architecture
Connectors	10/100/1000 copper: 4x RJ-45 with AutoCross™ (Auto MDI/MDI-X), 4 100/1000 SFP ports, 1 RS-232 D B-9 Female
MAC Address	8K MAC address table
Packet Buffer	1 Mbps
Network Cable	10BASE-T: 2-pair UTP/STP Cat. 3, 4, 5 cable; EIA/TIA-568 100-ohm (100 m) 100BASE-TX: 2-pair UTP/STP Cat. 5 cable; EIA/TIA-568 100-ohm (100 m); 1000BASE-T: 4-pair UTP/STP Cat. 5e cable; EIA/TIA-568 100-ohm (100 m)
Backplane	16 Gbps
LEDs	RJ-45 port: 10/100/1000; Link/Activity; Full duplex/Collision Fiber: Link/Activity Power: On/Off
Power Supply	Internal power: 100 – 240 VAC 50/60 Hz
Power Consumption	15 Watts max.
Operation Temperature	0° to 45°C (32° to 113°F)
Operation Humidity	10% to 90% (non-condensing)
Dimensions	Width: 8.54" [217 mm] Depth: 5.51" [140 mm] Height: 1.69" [43 mm]
EMI	FCC Class A, CE Mark
Safety Compliance	UL, cUL
Technical Support & Warranty	Free technical support and advanced warranty support for 5 years. Includes free telephone support, 24-hour support via web and FTP.

Ordering Information

MIL-SM4004TG

4-port 10/100/1000
Remotely Managed switch with
(4) Dual-Speed SFP Ports

Optional Accessories (sold separately)

SFP Modules

Mounting Bracket

MIL-RMSM8

19" Rack Mount Bracket

MIL-BRSM8

Wall Mount Bracket

Software Features

- ▶ **Management:**
Remote IP-Based Management, Web Management, SNMP v1/2/3, Telnet, Menu based CLI
- ▶ **Firmware update:**
TFTP firmware upgrade and configuration backup
- ▶ **System default:**
Restore function for system default
- ▶ **Port Trunk:**
Supports IEEE 802.3ad port trunk with link aggregation control protocol (LACP). The trunk group up to 2 and maximum trunk port member up to 2 ports.
- ▶ **VLAN:**
Port based-VLAN; IEEE802.1Q Tag based VLAN (256 entries), VLAN ID up to 4094, QinQ, 256 GVRP groups
- ▶ **Quality of Service:**
Support port based, Tag based and IPv4 ToS
- ▶ **Class of Service:**
4 priority queues
- ▶ **Spanning Tree:**
Supports IEEE 802.1w rapid spanning tree and IEEE 802.1d
- ▶ **Port Mirror:**
Supports TX/RX/Bi-Directional packet mirror
- ▶ **IGMP:**
Supports IGMP V1, V2
- ▶ **Storm Control**
Bandwidth Allocation on Broadcast