



stand-alone industrial device server

# SDSFE3110-120

## Remotely Managed Device Server




Transition Networks' Device Servers provide a serial-to-Ethernet conversion to enable customers to integrate any legacy serial-based device into their Ethernet networks. Network-enable serial based devices quickly and cost-effectively with these serial-to-Ethernet device servers. The device server can connect to RS-232, RS-422 or RS-485 serial ports and provides a 10/100BASE-TX Ethernet connection.

### Features

- ▶ AutoCross™
- ▶ Auto-Negotiation
- ▶ Remote Management
- ▶ Supports asynchronous serial data rates up to 115 Kbps
- ▶ Supports RS-232, 4-wire RS-422 or 2/4-wire RS485 operation
- ▶ Control up to 4,096 virtual COM ports from one PC
- ▶ DIN Rail Mounting
- Brackets included

### Network Enable Serial Devices



### Ordering Information

**SDSFE3110-120**

DB-9 [15 m/49 ft.]\*

to RJ-45 [100 m/328 ft.]

*\*Max. distance on the serial port is dependent on protocol:  
15 m/49 ft. (RS-232)  
1.2 km/0.7 mi. (RS-422/485)*

### Specifications

|                 |   |
|-----------------|---|
| Standards       | EIA/TIA RS-232/422/485, EIA/TIA-574, IEEE Std. 802.3  |
| Data Rate       | <b>Serial:</b> 115 Kbps<br><b>RJ-45:</b> 10/100 Mbps  |
| Drivers         | Windows 95, 98, ME, 2000, 2003, XP, NT 4.0<br>Microsoft NT/2000/2003 Terminal Server  |
| Switches        | <b>Switch 1:</b> ON = console serial port (RS-232); OFF = data serial port<br><b>Switch 2:</b> RS-232 mode on/off<br><b>Switch 3:</b> RS-422/485 (4-wire) mode on/off<br><b>Switch 4:</b> RS-485 (2-wire) mode on/off<br><b>Switch 7:</b> Termination resistor on/off     |
| Status LEDs     | <b>PWR (Power):</b> ON = power connected<br><b>100 (RJ-45):</b> ON = Link at 100 Mbps<br><b>LNK/ACT (RJ-45):</b> ON = UTP link;<br>FLASHING = activity<br><b>POST:</b> ON = Power On Self Test successful<br><b>ACT (serial):</b> ON = Serial link<br>FLASHING = activity |
| Dimensions      | Width: 3.5" [90 mm]<br>Depth: 4.3" [109 mm]<br>Height: 1.3" [32 mm]   |
| Input Power     | External AC/DC; 9 to 32 VDC, 0.8A   |
| Environment     | 0 to +50°C std. Operating temp.<br>5 – 90% humidity non-condensing;<br>0 – 10,000 ft. altitude  |
| Shipping Weight | 2 lb. [0.90 kg]   |
| Compliance      | CISPR22/EN55022 Class A + EN55024; EN60950 Class A; FCC Class A; CE Mark  |
| Warranty        | Lifetime  |