

13U SmartRack 2-Post Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: **SR2POST13**



Highlights

- 13U 2-post open frame rack
- Black aluminum with round threaded and numbered mounting holes

Package Includes

- SR2POST13
- 28 pieces each of 12-24 screws and washers for equipment mounting
- Installation hardware
- Cable management hooks
- Warranty Information
- Owner's Manual

Description

Tripp Lite's SR2POST13 2-Post SmartRack Open Frame Rack is an economical way to accommodate 13U of rack space for 19-inch rackmount applications in limited spaces. Its heavy-duty, aluminum construction can safely support 800 lbs. of rackmount equipment. The black, textured powder coat finish makes it resistant to scratching while giving it a "classic," attractive appearance. The SR2POST13 is easy to install due to a self-squaring design combined with numbered mounting positions and bolt down provisions. Only standard hand tools are required for installation (9/16" wrench and 9/16" socket/ratchet). Multiple units can be bolted together side by side for easy expansion or customization as needed. The SR2POST13 2-Post SmartRack Open Frame Rack has been approved by EIA-310-D, IEC 60297-3-100, DIN 41494 and RoHS, and is backed by a 5-year warranty.

Features

- Supports 800lbs of rackmount equipment
- Textured powder coat finish
- Heavy Duty Aluminum construction
- Numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly

Specifications

OVERVIEW	
Style	2-Post
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Installed Whole System Maximum Rack Depth (in.)	4.8
Installed Whole System Maximum Rack Depth (cm)	12.19
Rack Height (U Spaces)	13
Shipping Dimensions (hwd / in.)	4.5 x 6.1 x 28
Shipping Dimensions (hwd / cm)	11.4 x 15.5 x 71.1
Shipping Weight (lbs.)	22.1
Shipping Weight (kg)	10.02
Unit Dimensions (hwd / in.)	28 x 20.3 x 4.75
Unit Weight (lbs.)	20
Unit Weight (kg)	9.07
Unit Dimensions (cm)	71 x 51.6 x 12.1
Color	Black
Weight Capacity - Stationary (lbs.)	800
Weight Capacity - Stationary (kg)	362.9
Hinged (Swings Away from Wall Bracket)	No
CERTIFICATIONS	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.