Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



1425A Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/422



For more Information please call

1-800-Belden1



General Description:

24 AWG stranded (7x32) TC conductors, Datalene® insulation, twisted pairs, overall Beldfoil shield (100% coverage), 24 AWG stranded TC drain wire, PVC jacket.

Physical Characteristics (Overall) Conductor AWG: # Pairs AWG Stranding Conductor Material 24 7x32 TC - Tinned Copper **Total Number of Conductors:** 30 Insulation Insulation Material: Insulation Trade Name Insulation Material Wall Thickness (in.) FPE - Foam Polyethylene | 0.013 **Outer Shield** Outer Shield Material: Outer Shield Trade Name Type Outer Shield Material Coverage (%) Tape | Aluminum Foil-Polyester Tape | 100 Outer Shield Drain Wire AWG: AWG Stranding Drain Wire Conductor Material 24 7x32 TC - Tinned Copper **Outer Jacket Outer Jacket Material:** Outer Jacket Material Nom. Wall Thickness (in.) PVC - Polyvinyl Chloride 0.040

Overall Cable

Overall Nominal Diameter: 0.455 in.

Pair

Pair Color Code Chart:

Number	Color				
1	White/Blue & Blue/White				
2	White/Orange & Orange/White				
3	White/Green & Green/White				
4	White/Brown & Brown/White				
5	White/Gray & Gray/White				
6	Red/Blue & Blue/Red				
7	Red/Orange & Orange/Red				
8	Red/Green & Green/Red				
9	Red/Brown & Brown/Red				
10	Red/Gray & Gray/Red				
11	Black/Blue & Blue/Black				
12	Black/Orange & Orange/Black				
13	Black/Green & Green/Black				
14	Black/Brown & Brown/Black				
15	Black/Gray & Gray/Black				

Mechanical Characteristics (Overall) Operating Temperature Range: -20°C To +80°C Non-UL Temperature Rating: 80°C (UL AWM Style 2919) Bulk Cable Weight: 90 lbs/1000 ft. Max. Recommended Pulling Tension: 165 lbs. Min. Bend Radius/Minor Axis: 4.750 in.

Page 1 of 3 01-09-2015

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION

-



1425A Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/422

Applicable Specifications and Agency Compliance (Overall)					
Applicable Standards & Environmental Programs					
NEC/(UL) Specification:	CM				
CEC/C(UL) Specification:	CM				
AWM Specification:	UL Style 2919 (30 V 80°C)				
EU Directive 2011/65/EU (ROHS II):	Yes				
EU CE Mark:	Yes				
EU Directive 2000/53/EC (ELV):	Yes				
EU Directive 2002/95/EC (RoHS):	Yes				
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004				
EU Directive 2002/96/EC (WEEE):	Yes				
EU Directive 2003/11/EC (BFR):	Yes				
CA Prop 65 (CJ for Wire & Cable):	Yes				
MII Order #39 (China RoHS):	Yes				
Flame Test					
UL Flame Test:	UL1685 UL Loading				
Plenum/Non-Plenum					
Plenum (Y/N):	No				

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:



Nom. Inductance:

Inductance (µH/ft)
.213

Nom. Capacitance Conductor to Conductor:



Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
22

Nominal Velocity of Propagation:

VP (%) 78

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 24

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 11.2

Max. Operating Voltage - UL:

 Voltage
 Description

 30 V RMS
 UL AWM Style 2919

 300 V RMS
 CM

Max. Recommended Current:

Current
1.8 Amps per conductor @ 25°C

Notes (Overall)

Notes: Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low distortion data handling. Physical properties include good crush resistance and light weight.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1425A 0601000	1,000 FT	97.000 LB	CHROME	С	15 PR #24 FRFPE FS PVC
1425A 060500	500 FT	52.500 LB	CHROME	С	15 PR #24 FRFPE FS PVC

Page 2 of 3 01-09-2015

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



1425A Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/422

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 09-11-2012

© 2015 Belden, Inc All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Page 3 of 3