

52U Heavy-Duty 4-Post SmartRack Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: **SR4POST52HD**



Highlights

- 52U Heavy-Duty 4-post open frame rack
- Black steel with square, numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Package Includes

- SR4POST52HD Heavy-Duty 4-Post Open Frame Rack
- Installation hardware
- (2x) PDU/Cable management brackets
- Owner's manual with warranty information

Description

SmartRack 4-post heavy-duty open frame racks are an economical solution for 19-inch rackmount applications.

Features

- Weight capacity of 3000 lbs. stationary
- Supports equipment depths up to 35 inches
- Textured, black powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Self-squaring design
- Easy assembly
- Optional SRCASTERHDKIT heavy-duty caster kit permits mobile use of 3,000 lb rolling loads
- Optional SR52SIDE4PHD side panels for end-of-the-row aesthetics

Specifications

OVERVIEW	
Style	4-Post
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	35.25



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Installed Whole System Maximum Rack Depth (cm)	89.54
Rack Height (U Spaces)	52
Shipping Dimensions (hwd / in.)	6.75 x 9.5 x 101
Shipping Dimensions (hwd / cm)	17.15 x 24.13 x 256.54
Shipping Weight (lbs.)	123
Shipping Weight (kg)	55.35
Unit Dimensions (hwd / in.)	97 x 24 x 35.25
Unit Weight (lbs.)	116
Unit Weight (kg)	52.2
Unit Dimensions (cm)	246.38 x 60.96 x 89.54
Color	Black
Weight Capacity - Stationary (lbs.)	3000
Weight Capacity - Stationary (kg)	1350
Hinged (Swings Away from Wall Bracket)	No
CERTIFICATIONS	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.