

## SmartRack 12U Slim Wall-Mount Standard-Depth Rack Enclosure Cabinet

MODEL NUMBER: **SRW12U13**



### Highlights

- Slim design for shallow network switches and patch panels
- 12U with dual threaded front rails
- Locking, reversible front door
- Locking, removable side panels
- Fully assembled for quick installation
- PCI-Compliant: meets stringent physical security requirements
- Interior vertical posts have square holes for cage nuts plus 12-24 threaded mounting holes

### Package Includes

- SRW12U13 Wallmount Rack Enclosure
- Mounting Hardware
- Keys
- Owner's Manual

### Description

The SRW12U13 slim 12U Wall-Mount Rack Enclosure is designed to safely store shallow network switches and patch panels. It integrates wall-mounting, easy equipment access and cable management in Telco environments with limited floor space. Ventilated top and bottom panels allows generous airflow to keep equipment operating safely. Top panel offers a convenient cable access cutout with cover. Adjustable front mounting rails have square holes (default position) and tapped holes to accommodate 12U of equipment. A sturdy wall-mount bracket allows the cabinet to quickly be hung on the wall and supports up to 200lbs of equipment. The SRW12U13 comes with a 5-year product warranty.

### Features

- 12U slim wall-mounted enclosure
- Dual threaded rail option
- Ventilated top and bottom panels for increased airflow
- Locking, reversible front door
- Locking, removable side panels
- Fully assembled for quick installation
- PCI-Compliant: meets stringent physical security requirements

## Specifications

OVERVIEW	
Style	Wall Mounted
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	13



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Rack Height (U Spaces)	12
Shipping Dimensions (hwd / in.)	27.56 x 25.6 x 15.75
Shipping Weight (lbs.)	40
Unit Dimensions (hwd / in.)	25.08 x 23.62 x 13
Unit Weight (lbs.)	38
Color	Black
Weight Capacity - Stationary (lbs.)	200
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Hinged (Swings Away from Wall Bracket)	No
<b>SPECIAL FEATURES</b>	
Grounding Lug	Front door frame
<b>CERTIFICATIONS</b>	
Certifications	EIA-310-E
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.