



## Surge Protection Devices T&B Catalog Number:

**UPC Number:**

OVRT22L15320PU

**Status:**

80432556430

**Description:**

Active

Two pole OVR DIN rail surge protection device with a surge capacity of 15 kA and maximum voltage of 320V

### Features

Fast acting metal oxide varistor (MOV) technology limits overvoltage to values compatible with the sensitive equipment connected to the network

Each cartridge is equipped with a mechanical end of life indicator

Pluggable cartridges allow replacement of dead cartridges without isolating the electrical circuit

### Application

For protecting valuable equipment against transient surges and to help keep operations up and running

Installation at branch panels, control panels and terminal equipment is recommended to provide the most complete protection.

### General

Mounting Method Din rail

Number of Poles 2

Terminal Type Screw

### Approvals

UL Class UL1449 3rd edition, type 4 recognized component

### Dimension Information

H x W x D (inches) 3.6 x 2.6 x 1.4

H x W x D (mm) 90.5 x 64.8 x 35.6

### Specifications

Current Less Than 0.1 mA

Maximum Continuous Operating Voltage (V) 320

Service Voltage-Delta 240V

Service Voltage-HLD 240/120V

Service Voltage-Single Phase 240V AND 277V

Service Voltage-Split Phase 480/240V

Service Voltage-Wye 480Y/277V

Surge Capacity (kA) 15

Voltage Protection Rating (kV) 1

Frequency Rating (Hz) 50 - 60

### Packaging

Package in Units 1

T&B Sold in UOM Each

T&B Weight Per UOM

56 lbs. per 100

### **Application Support**

Product Brochure

Available on Website

#### **For further technical assistance, please contact us...**

ABB, Inc.  
Low Voltage Products  
16250 W. Glendale Drive  
New Berlin, WI 53151  
Phone: 888-385-1211  
Fax: 800-726-1411

USA Technical Support & Customer Service  
888-385-1211, Option 4  
7:30AM to 5:30PM, CST  
Monday - Friday  
Email: [lvps.support@us.abb.com](mailto:lvps.support@us.abb.com)