



Type A-Non-Metallic Liquidtight Conduit & Fittings

T&B Catalog Number:

UPC Number:

6302

Status:

78621006302

Description:

Active

1/2 Inch non-metallic Type A liquidtight connector with captive sealing O-ring and tapered hub thread.

Features

Serrated design provides high mechanical pull-out strength.

Unique component parts (body/gland) design ensures positive seal between conduit and connector.

Tapered thread hub and furnished neoprene sealing O-ring provide a liquidtight, dust-tight seal to a box or enclosure.

Smooth insulated body throughout for maximum dielectric strength.

Captive O-ring and reduced number of parts save installation time.

Application

To provide a liquidtight, dust tight connection between flexible, non-metallic conduit and a box or an enclosure.

Chemical resistant, ideal for corrosive environments

Ideal for automotive and automotive OEM applications, electric signs and outdoor lighting over 1000V (Article 600.31(A)), and pool and spa wiring. (Article 680)

General

Trade Size (inches)

1/2

Material

Thermoplastic

Dimension Information

Dimension A (inches)

0.6

Dimension B (inches)

1.68

Dimension C (inches)

1.48

Specifications

3dmodel

Available on Website

Packaging

T&B Inner Pack

20

Package in Units

100

T&B Sold in UOM

Each

T&B Weight Per UOM

11.56 lbs. per 100

Application Support

Product Brochure-Type A Liquidtight Connectors & Conduit Available on Website

Product Overview-Type A Liquidtight Flexible Non-Metallic Conduit & Connectors Available on Website

Guide to Nonmetallic Conduit Applications Available on Website

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com