

SmartRack 5U Low-Profile Wall-Mount Rack Enclosure Cabinet - 36 in. max horizontal mounting depth

MODEL NUMBER: **SRWF5U36**



Description

The SRWF5U36 5U+2 Low-Profile Wall Mount Rack Enclosure Cabinet is designed to integrate wall-mounting, easy equipment access and cable management in IT network applications with limited floor space. Ventilated front door and bottom panels allow generous airflow to keep equipment operating safely. Adjustable horizontal rack rails securely mount 5U of 19" rackmount equipment with M6 or they can be reversed for securing with 12-24 threaded mounting holes. The patch panel mounting brackets provide space for up to 2U of patch panels with integral slide-out feature for easy cable access. Supports up to 150 lbs. of equipment.

Features

- 5U low-profile wall-mounted enclosure
- Adjustable horizontal mounting depths from 33" to 36" inches
- Slide-out mounting brackets provides 2U of space for patch panel(s)
- Ventilated front door and bottom panels for increased airflow
- Locking, reversible front door
- Multiple keyhole mounting slots for wall mounting
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) compliance

Highlights

- Designed for IT and education environments where equipment needs to be secure and out of the way
- 5U with adjustable/reversible rackmount rails
- 2U slide-out mounting brackets for patch panels
- Locking, reversible front door
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance

Package Includes

- SRWF5U Low-profile wall-mount enclosure
- (12) M6 screws
- (12) M6 cup washers
- (12) 12-24 screws
- (2) Keys
- Owner's Manual

Specifications

OVERVIEW	
Application	IT network environments, back office, and network closets with limited floor space and classrooms where equipment needs to be secure and out of the way of students.
Style	Wall Mounted



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	36
Installed Whole System Maximum Rack Depth (cm)	91.44
Installed Whole System Minimum Rack Depth (in.)	33
Installed Whole System Minimum Rack Depth (cm)	83.82
Rack Height (U Spaces)	5
Shipping Dimensions (hwd / in.)	45.5 x 28 x 12
Shipping Dimensions (hwd / cm)	115.57 x 71.12 x 30.48
Shipping Weight (lbs.)	77.8
Shipping Weight (kg)	35
Unit Dimensions (hwd / in.)	43.2 x 25.6 x 9.7
Unit Weight (lbs.)	55
Unit Weight (kg)	25
Unit Dimensions (cm)	109.72 x 65.02 x 24.63
Color	Black
Weight Capacity - Stationary (lbs.)	150
Weight Capacity - Stationary (kg)	68.0
Hinged (Swings Away from Wall Bracket)	No
CERTIFICATIONS	
Certifications	EIA-310-E
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.