

## SmartRack Roof-Mounted Fan Panel - 6 208/240V high-performance fans; 420 CFM; C14 inlet

MODEL NUMBER: SRXFANROOF



### Highlights

- Roof Mount Fan Panel - 208-240V
- Ideal for increasing the ventilation of SmartRacks
- Features (6) 208-240V fans mounted in a roof panel
- Toolless mounting hardware included
- Cold rolled steel with black finish

### Package Includes

- SRXFANROOF 208-240V 50/60Hz fan roof
- Toolless mounting hardware
- 6 inch C14 inlet dongle (user-supplied input cord required)

### Description

Tripp Lite's SmartRack SRXFANROOF is ideal for increasing the ventilation in all rack enclosure server cabinets. The unit features (6) 208-240V high performance fans mounted in a roof panel, and includes toolless mounting hardware. Built-in cable access holes for routing of cables through fan roof panel. Supports 208-240V 50/60 Hz AC input.

COMPATIBLE SMARTRACK ENCLOSURES - SR25UB, SR25UBKD, SR25UBSP1, SR25UBTAA, SR42UB, SR42UBCL, SR42UBEXP, SR42UBG, SR42UBKD, SR42UBSP1, SR42UBTAA, SR48UB, SR48UBCL, SR48UBEXP, SR48UBSP1, SR42UBTAA, and other Tripp Lite SmartRack enclosures that specify the use of this accessory.

### Features

- Ideal for increasing the ventilation in all rack enclosure server cabinets
- Features (6) 208-240V high performance fans mounted in a roof panel
- Includes toolless mounting hardware
- Built-in cable access holes for routing of cables through fan roof panel
- Supports 208-240V 50/60 Hz AC input
- Compatible SmartRack Enclosures: SR25UB, SR25UBKD, SR25UBSP1, SR25UBTAA, SR42UB, SR42UBCL, SR42UBEXP, SR42UBG, SR42UBKD, SR42UBSP1, SR42UBTAA, SR48UB, SR48UBCL, SR48UBEXP, SR48UBSP1, SR42UBTAA, and other Tripp Lite SmartRack enclosures that specify the use of this accessory

## Specifications

OVERVIEW	
Model Type	Passive Cooling
Accessories Type	Fan Panel



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>INPUT</b>	
Nominal Input Voltage(s) Supported	208V AC; 230V AC; 240V AC
Nominal Input Voltage Description	208-240V AC 50/60 Hz
Input Connection Type	IEC C14 inlet dongle (user-supplied input cord required)
Cable Length (in.)	6
Voltage Compatibility (VAC)	208; 230; 240
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	15 x 23.3 x 27
Shipping Dimensions (hwd / cm)	38.1 x 59.18 x 68.58
Shipping Weight (lbs.)	25
Shipping Weight (kg)	11.34
Unit Dimensions (hwd / in.)	2.1 x 21.9 x 35.5
Unit Weight (lbs.)	22
Unit Weight (kg)	9.98
Unit Dimensions (cm)	5.33 x 55.63 x 90.17
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.