


Gallagher T20 Terminal



Gallagher T20 Terminal allows site wide alarms management with ease of use and full implementation flexibility.

- Contemporary and intuitive user interface, with a 3.5" colour LED screen and large backlit keys
- Clear display icons for key access control tasks
- Superior ingress and impact protection, IP66 environmental protection and IK08 for impact protection
- Card only and card + PIN access modes (including duress access support)
- Alarm Zone arming and disarming of up to 50 alarm zones distributed across any system controllers
- Dynamic display of up to 200 unacknowledged alarms and 100 acknowledged alarms for up to four weeks
- Management of up to 100 inputs
- Fully configurable Mimic Panel reflecting the status of up to 8 inputs, outputs, or alarm zones
- Configurable arming workflow including automated input isolation
- Configurable disarming workflow (optional automated alarms acknowledgement and display)
- Dual cardholder authentication
- Terminal based access mode selection
- Door alarm zone arming/disarming
- Enforce cardholder compliance with entry regulations through competency message display
- Fully up-gradeable software to keep your system up to date with latest technology developments (via HBUS)
- Ability to perform automatic software updates in situ
- Multiple language support
- Integrated rear tamper



Gallagher T-Series accessories:

- Protective Covers - IK08 rating protects readers against vandal attacks and harsh environments
- Dress Plates - Ensure a clean finish for sites upgrading their reader and terminal hardware
- Spacers - enforces a space between the reader and the mounting surface, allowing installations on metal surfaces whilst preserving credential read range
- Bezels - surrounds available in a variety of colours to suit décor



GALLAGHER T20 TERMINAL		FEBRUARY 2015	
TECHNOLOGY AND READ DISTANCE*	Mifare / Multi Mode		
Mifare Classic	80mm		
Mifare Plus, DESFire	40mm		
125kHz	95mm		
POWER SUPPLY	Mifare Mode	Multi Mode	Alarm Terminal
Voltage	9-16Vdc		
Idle current @ 13.6Vdc	140mA	189mA	110mA
DIMENSIONS	mm	Inches	
	179.5 x 95.7 x23	7.1 x 3.8 x0.9	
DATA CABLE SPECIFICATIONS°			
2 wire, RS485 data cable (Cat5, Belden 9842 or equivalent) HBUS-500M; Cardax IV- 200M			
ENVIRONMENTAL SPECIFICATIONS			
Temperature Range	-30° to + 70°C (-22°F to +158°F)		
Humidity	95% non-condensing		
Environmental protection	IP66		
Impact rating	IK08		
UV Stability	Nil structural degradation for the life of the reader*		
Standards Compliance	All equipment complies with FCC, CE and C-Tick approvals. Please contact Gallagher for the latest list of approvals.		
* Read range may be reduced when reader is mounted on metal surfaces			
* Prolonged exposure to high UV light environments can cause plastics to discolor			
° For further cable specifications please refer to the Gallagher Security System Technical Reference Manual			

T20 ORDER CODES	
T-Series Terminals	
C300461	T20 Multi Tech Reader, White
C300460	T20 Multi Tech Reader, Black
C300451	T20 Mifare Reader, White
C300450	T20 Mifare Reader, Black
T-Series Alarms Only Terminals	
C300464	T20 Alarms Terminal, White
C300463	T20 Alarms Terminal, Black
T-Series Dress Plates	
C300323	T20 Dress Plate, Black, Pk 5
T-Series Bezels	
C300292	T20 Bezel, Black, Pk 5
C300293	T20 Bezel, White, Pk 5
C300294	T20 Bezel, Silver, Pk 5
C300295	T20 Bezel, Gold, Pk 5
T-Series Spacers	
C300306	T20 Spacer, Black, Pk 5
C300307	T20 Spacer, White, Pk 5
C300312	T20 Protective Cover Spacer
T-Series Protective Covers	
C300272	T20 Protective Cover

T20 PROTECTIVE COVER	
Dimensions (H X W X D)	
193mm x 123mm x 32mm	

©2013 Gallagher Group Ltd. Gallagher is an ISO 9001:2008 certified supplier. All rights reserved. The products described in this document are subject to continuous development and improvement so specifications and information may change without notice. System configuration, network capacities and the volume of system activity affect performance.

GALLAGHER WORLD HEADQUARTERS

Kahikatea Drive, Hamilton 3206
Private Bag 3026, Hamilton 3240
New Zealand

TEL: +64 7 838 9800

EMAIL: sales@security.gallagher.com

REGIONAL OFFICES

New Zealand..... +64 7 838 9800
Americas..... +1 877 560 6308
Asia +852 3468 5175
Australia +61 3 9308 7722
India +91 80 2661 1590
Middle East..... +9615 808728
South Africa +27 11 974 4740
United Kingdom / Europe..... +44 2476 64 1234

Disclaimer: System configuration, network capacities and the volume of system activity affect performance. Please contact Gallagher for advice. In accordance with the Gallagher policy of continuing development, design and specifications are subject to change without notice. Gallagher Group Limited is an ISO 9001:2008 Certified Supplier. Copyright © Gallagher Group Limited 2012. All rights reserved.

