

## 3-Breaker Parallel Tie Cabinet with Maintenance Bypass Switch (for SU80KX 3-Phase UPS)

MODEL NUMBER: **SUPC4MBP80KX**



### Highlights

- 3 breaker parallel tie cabinet accessory for four Tripp Lite 80kVA 3 phase UPS systems
- Links the output of four UPS systems for 320kVA non-redundant operation
- Integral Maintenance Bypass switch enables UPS maintenance or replacement
- 3 built-in circuit breakers, heavy duty copper buswork
- Compatible with Tripp Lite SU80KX 3 phase UPS systems

### Description

Tripp Lite's parallel tie cabinet provides a means for safely paralleling two UPS systems for non-redundant combined mode operation. Non-redundant configuration combines the output of four UPS systems to support four times the output current. Built-in Maintenance Bypass Switch enables UPS maintenance and repair of with no disruption in power to connected equipment. Two input breakers receive incoming power from the UPS and are connected to heavy duty copper buswork and an output breaker rated for the total UPS capacity of the two UPS systems combined. See owners manual and [Tripp Lite Parallel Tie Cabinet with Bypass Panel](#) download for detailed specifications, dimensional drawings, operational flow charts and technical descriptions.

Compatible with four Tripp Lite SU80KX UPS systems.

### Features

- Provides a means for safely paralleling two UPS systems for non-redundant combined mode operation
- Non-redundant configuration combines the output of four UPS systems to support four times the output current
- Built-in Maintenance Bypass Switch enables UPS maintenance and repair of with no disruption in power to connected equipment
- Two input breakers receive incoming power from the UPS and are connected to heavy duty copper buswork and an output breaker rated for the total UPS capacity of the two UPS systems combined
- Compatible with four Tripp Lite SU80KX UPS systems

## Specifications

OVERVIEW	
Model Type	Tie Cabinets
Accessories Type	Parallel Tie Cabinet
INPUT	
Nominal Input Voltage(s) Supported	380V AC; 400V AC; 415V AC



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Voltage Compatibility (VAC)	380; 400; 415
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	70.25 x 38.88 x 12.5
Shipping Dimensions (hwd / cm)	178.4 x 98.75 x 31.75
Shipping Weight (lbs.)	490
Shipping Weight (kg)	222.5
Unit Dimensions (hwd / in.)	69.5 x 38.1 x 11.8
Unit Dimensions (hwd / cm)	176.5 x 96.8 x 30
Unit Weight (lbs.)	485
Unit Weight (kg)	220.2
Form Factors Supported	Wallmount
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.