




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NUMBER	TYPE	FOR USE WITH
FLCSS3.0BU	SINGLEMODE	9/125um FIBER
FLCSM3.0BL	MULTIMODE	50/125um FIBER
FLCSM3.0EI	MULTIMODE	62.5/125um FIBER

NOTES:

1. SEE CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. ACCEPTS 3.0mm 9/125um SINGLEMODE, 50/125um MULTIMODE OR 62.5/125um MULTIMODE GLASS OPTICAL FIBER.
3. FULLY COMPLIES WITH THE FIBER OPTIC CONNECTOR PERFORMANCE REQUIREMENTS AS SPECIFIED BY TIA/EIA-568-B.3.
4. MATERIAL:
BODY/HARDWARE: PLASTIC
BOOT: THERMOPLASTIC RUBBER
FERRULE: ZIRCONIA CERAMIC
5. DIMENSIONS IN BRACKETS ARE METRIC [mm].
6. WEIGHT PER 10 PIECES: .037 lb [16.7g].



											FIBER OPTIC SINGLEMODE/MULTIMODE SIMPLEX LC CONNECTOR WITH 3.0mm BOOT CUSTOMER DRAWING		
												 TINLEY PARK, ILL 60477	
											 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (.0.3) (.XX) ± .03 (.0.8) ANGLES	DRAWING FILENAME M01371ZU_DC/01A
													SCALE NONE
											DRAWN BY MC	REVIEW DRAWING NUMBERS	PART NO. FLCSS3.0BU FLCSS3.0BL/FLCSM3.0E
1	04-15-10	MC		RELEASED TO PRODUCTION	01371-51						DATE 09-17-07	DRAWING NO. 01371-51	SIZE A
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	CHK'D	JDK			