

DUPLEX LC
PORTSVIEW SHOWN WITHOUT
DUSTCAPS

PANDUIT PART NUMBER	FIBER TYPE	PERFORMANCE LEVEL	ADAPTER COLOR (SPLIT SLEEVE)
FQXN-12-10AF	OM3	STANDARD LOSS	AQUA (ZIRCONIA)
FOXO-12-10AF	OM3	OPTIMIZED LOSS	AQUA (ZIRCONIA)
FQZN-12-10AF	OM4	STANDARD LOSS	AQUA (ZIRCONIA)
FQZO-12-10AF	OM4	OPTIMIZED LOSS	AQUA (ZIRCONIA)
FOSA-12-10AF	OM4+ (SIG CORE)	ULTRA LOW LOSS	AQUA (ZIRCONIA)
FQ9N-12-10AF	OS1/OS2	STANDARD LOSS	BLUE (ZIRCONIA)

NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. MATERIALS:
 - A. MODULE MATERIAL: PLASTIC
 - B. ADAPTER: COMPOSITE PLASTIC
4. CASSETTE MODULE WEIGHT: 2.4oz (69.0g)
5. DIMENSIONS IN BRACKETS ARE METRIC
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTIONS OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

QUICKNET SFO SERIES CASSETTE, 12 FIBER DUPLEX
LC TO MPO MODIFIED METHOD A, PAIR FLIPPED
CUSTOMER DRAWING**PANDUIT**™
CORP.
TINLEY PARK, ILL 60477THIRD ANGLE
PROJECTIONALL DIMENSIONS ARE GIVEN IN INCHES,
UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX)±.010 (0.3)
(.XX)±.03 (0.8) ANGLESDRAWING FILENAME
MO2947ZD_DC/02ASCALE
NONEDRAWN BY
EFK

REVIEW DRAWING NUMBERS

PART NO.
FQ**-12-10AFDATE
09-19-08DRAWING NO.
02947-30SIZE
A

4 12-04-12 SAT JESA RELEASED TO PRODUCTION

02947-30 JESA CHDE

REV DATE BY CHK DESCRIPTION

ECN - R CUST SUP OTH

CHK'D
WMA