




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. DIAMETER DIMENSION SHOWN FOR REFERENCE ONLY.
2. PLENUM-RATED CABLES MEET THE REQUIREMENTS OF NFPA 262.
RISER-RATED CABLES MEET THE REQUIREMENTS OF UL 1666.
3. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.




PLENUM			
TENSILE LOAD		BEND RADIUS	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
400 lbs (1800 N)	120 lbs (540 N)	11.0 in (28 cm)	5.5 in (14 cm)
CABLE DIAMETER (REFERENCE ONLY)	TEMPERATURE		
	STORAGE/OPERATION		INSTALLATION
.55" [13.9 mm]	-40°F TO +176°F [-40°C TO +80°C]		32°F TO +140°F [0°C TO +60°C]
RISER RATED			
TENSILE LOAD		BEND RADIUS	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
600 lbs (2670 N)	180 lbs (800 N)	13.2 in (33.6 cm)	6.6 in (16.8 cm)
CABLE DIAMETER (REFERENCE ONLY)	TEMPERATURE		
	STORAGE/OPERATION		INSTALLATION
0.66" [16.8 mm]	-40°F TO +176°F [-40°C TO +80°C]		14°F TO +140°F [-10°C TO +60°C]

							TITLE 48 FIBER INDOOR/OUTDOOR CABLE WITH 900um BUFFERED FIBERS CUSTOMER DRAWING					
							ITEM REVISION NAME M02055JD/00					
							DATASET FILE NAME M02055JD_DC/00A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±					
							 THIRD ANGLE PROJECTION					
00	02-04-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055JD-DC	PART NO. SEE TABLE DRAWING NUMBER: M02055JD-DC					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SIZE	
							SAT	02-04-14	WMA	NONE	SHT 1 OF 2 A	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	FLAME RATING	CABLE ATTENUATION
FSLP548	MULTIMODE 50/125 OM2 INDOOR/OUTDOOR CABLE	OFNP	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FSLR548		OFNR	
FSLP648	MULTIMODE 62.5/125 OM1 INDOOR/OUTDOOR CABLE	OFNP	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FSLR648		OFNR	
FOLPX48	MULTIMODE 50/125 OM3 INDOOR/OUTDOOR CABLE	OFNP	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FOLRX48		OFNR	
FOLPZ48	MULTIMODE 50/125 OM4 INDOOR/OUTDOOR CABLE	OFNP	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FOLRZ48		OFNR	
FSLP948	SINGLEMODE 9/125 INDOOR/OUTDOOR CABLE	OFNP	0.7dB/km @ 1310nm 0.7dB/km @ 1550nm
FSLR948		OFNR	

							TITLE					
							48 FIBER INDOOR/OUTDOOR CABLE WITH 900um BUFFERED FIBERS					
							CUSTOMER DRAWING					
							ITEM REVISION NAME M02055JD/00		PANDUIT			
							DATASET FILE NAME M02055JD_DC/00A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		PART NO.			
							.X ± .XXX ± .010 (0.3) .XX ± .03 (0.8) ANGLES ±		SEE TABLE			
							 THIRD ANGLE PROJECTION		DRAWING NUMBER: M02055JD-DC			
00	02-04-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055JD-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 02-04-14	CHK WMA	SCALE NONE	SHT 2 OF 2	SIZE A