



FC Adaptors



We offer a range of high quality FC adaptors featuring precision alignment sleeves for high reliability and better reconnectability. FC adaptors come with ceramic sleeves for singlemode and phosphor bronze sleeve for multimode. The housing has a metal body, a M8 nut and Double D footprint.

FEATURES

- Complies with IEC 61754-13 and TIA 604-4-A
- High precision alignment sleeve for low insertion loss
- Low insertion loss and high reconnectability
- Narrow key, 2.06mm for APC and PC connectors
- REACH SvHC compliant
- Materials compliant to RoHS2
- Available in simplex only with DD footprint

APPLICATIONS

- Telecommunications networks
- Local area networks
- Data processing networks
- Cable television
- Premises distribution
- Test and laboratory equipment
- Industrial and military application


SPECIFICATION

| | CERAMIC | PHOSPHOR BRONZE | CONFORMANCE |
|----------------------------|-----------------------|-----------------------|----------------|
| Insertion Loss (Typ) | 0.1 dB | 0.15 dB | IEC 61300-3-4 |
| Mating Durability | 500 | 500 | IEC 61300-2-2 |
| Receptacle Retention Force | 2N - 5.9N | 2N - 5.9N | IEC 61754-13 |
| Operating Temperature | -25 to +70, 12 cycles | -25 to +70, 12 cycles | IEC 61300-2-22 |

ORDERING INFORMATION

| DESCRIPTION | PART NO. |
|------------------------------------|--------------------|
| DD mount type - Singlemode APC | FCAPCUZRO2-DD/Z |
| DD mount type - Singlemode PC | FCUZRO2-DD/Z |
| DD mount type - Multimode PC | FCUPHBR-DD/Z |
| Square mount type - Singlemode APC | FCAPCUZRO2SQUARE/Z |
| Square mount type - Singlemode PC | FCUZRO2SQUARE/Z |
| Square mount type - Multimode PC | FCUPHBR2SQUARE/Z |

Please contact our sales team on +44 (0) 1908 441 121 for further ordering information.



CONTACT OUR SALES TEAM TODAY

Europe: +44 1908 441 100 | sales@optronicsnet.com

Americas: +1 410 242 9026 | sales@optronicsnet.com

Asia Pacific: +86 755 2531 3694 | apac@optronicsnet.com

Middle East & Africa: +971 4 443 1028 | mea@optronicsnet.com

Web: www.optronicsnet.com