


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:


- VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- COMPONENTS:  
PEVBRC6 CONTAINS (4) CLIPS  
PEVBRC8 CONTAINS (4) CLIPS  
PEVBRC10 CONTAINS (4) CLIPS  
PEVBRC12 CONTAINS (4) CLIPS
- DIMENSIONS IN PARENTHESIS ARE METRIC.

← "X" ± .125 (±3) →




| PANDUIT P/N | "X" IN (mm) | WEIGHT                      |
|-------------|-------------|-----------------------------|
| PEVBRC6     | 5.1 (130)   | 1.6 LBS/EACH<br>0.7 Kg/EACH |
| PEVBRC8     | 7.1 (180)   | 2.0 LBS/EACH<br>0.9 Kg/EACH |
| PEVBRC10    | 9.1 (231)   | 2.4 LBS/EACH<br>1.1 Kg/EACH |
| PEVBRC12    | 11.1 (307)  | 2.8 LBS/EACH<br>1.3 Kg/EACH |

BEND RADIUS  
CLIP FOR SMOOTH  
TRANSITION FOR  
FRONT TO BACK  
CABLING



PEV VERTICAL MANAGER  
CENTER PANEL

|     |         |      |      |      |                  |             |                                                                                                                    |                 |     |                                                                                       |                                  |                          |
|-----|---------|------|------|------|------------------|-------------|--------------------------------------------------------------------------------------------------------------------|-----------------|-----|---------------------------------------------------------------------------------------|----------------------------------|--------------------------|
|     |         |      |      |      |                  |             | TITLE<br><br>PATCHRUNNER HIGH CAPACITY VERTICAL<br>MANAGER BEND RADIUS CLIP KIT (PEVBR CX)<br><br>CUSTOMER DRAWING |                 |     |                                                                                       |                                  |                          |
|     |         |      |      |      |                  |             | ITEM REVISION NAME<br><br>10V179BE/00                                                                              |                 |     |  |                                  |                          |
|     |         |      |      |      |                  |             | DATASET FILE NAME<br><br>10V179BE_DC/00B                                                                           |                 |     |                                                                                       |                                  |                          |
|     |         |      |      |      |                  |             | UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:                                                            |                 |     |                                                                                       |                                  |                          |
| 00B | 5-27-15 | TWV  | BAME | KRKE | ADDED VIEW       | 10V179BE-DC | INCHES<br>X.X +/- 0.03<br>X.XX +/- 0.018<br>X.XXX +/- 0.007                                                        |                 |     | METRIC - MILLIMETER<br>X. +/- 0.8<br>X.X +/- 0.46<br>X.XX +/- 0.18                    | ANGLE<br>+/- 1°                  | MATERIAL:<br><br>PLASTIC |
| 00A | 3-21-11 | BAME |      |      | DRAWING RELEASED | 10V179BE-DC |                               |                 |     | THIRD ANGLE<br>PROJECTION                                                             | DRAWING NUMBER:<br>10V179BE - DC |                          |
| REV | DATE    | BY   | CHK  | APR  | DESCRIPTION      | ECN         | DRAWN BY<br>BAME                                                                                                   | DATE<br>3-21-11 | CHK | SCALE<br>NONE                                                                         | SHT 1 OF 1                       | SIZE<br>A                |