


1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6) C-19 NETWORKED
208V / 20A / THREE-PHASE WYE POU



2. ACCESSORY COMPONENTS:
 (4) #10-32 x 1/2" MOUNTING SCREWS
 (4) #12-24 x 1/2" MOUNTING SCREWS
 (2) #10-32 LOCKING COLLAR SCREWS
 (2) L-BRACKETS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).

4. CURRENT METER - RED, 4-DIGIT LED DISPLAY PROVIDES TRUE RMS CURRENT THAT CONTINUOUSLY SCROLLS THROUGH THE THREE DIFFERENT MEASURED CIRCUITS. METER DISPLAYS CIRCUIT NAME FOLLOWED BY THE MEASURED CURRENT (E.G. CR-1 REPRESENTS PHASE 1). CIRCUIT (XY,YZ,ZX) LEVEL MONITORING CAN ALSO BE ACCESSED REMOTELY VIA ETHERNET CONNECTION.

5. UL® & c-UL® LISTED 60950 AND NOM COMPLIANT.




6. RoHS COMPLIANT.

7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.

8. MAXIMUM AVAILABLE INPUT POWER = 5.7 KW

9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.

— 10 FOOT INLET POWER CORD



01A	8-30-12	PIP	MRWA	A. UPDATED NOTE #5 & 8. B. ADDED NOTE #9.	09V098NB					
00A	11-22-10	MAV	KRKE	RELEASED TO PRODUCTION	09V098NB					
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH		

MODEL FILENAME		09V098NB/01.PRT	
CAD FILENAME/LAYERS		09V098NB_DC/01A.PRT	
PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, MIXED (24) C-13 & (6) C-19 NETWORKED POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		[METRIC - MILLIMETER] X. +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13	
ANGLE +/- 1°		ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY MAV		SCALE NONE	
DATE 11-22-10		DRAWING NO. 09V098NB	
CHK'D KRKE		DWG B	