

1818P Multi-Conductor - CMP Rated Cable



For more Information
please call

1-800-Belden1

**General Description:**

22 AWG stranded (7x30) TC conductor, polyolefin insulation, individually shielded with bonded Beldfoil®, numbered/color-coded solef jackets, jackets and shields are bonded so both strip simultaneously, overall fluorocopolymer jacket and nylon rip cord.

Usage (Overall)

Suitable Applications: Outdoor Applications, Sports Stadium

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
12	22	7x30	TC - Tinned Copper	0.030

Total Number of Conductors: 24

Insulation

Insulation Material:

Insulation Material
FEP

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
22

Inner Shield Drain Wire Stranding: 7x30

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (in.)
PVDF	0.119

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVDF

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Gray #1
2	Gray #2
3	Gray #3
4	Gray #4
5	Gray #5
6	Gray #6
7	Gray #7
8	Gray #8
9	Gray #9
10	Gray #10
11	Gray #11
12	Gray #12

Overall Nominal Diameter: 0.524 in.

1818P Multi-Conductor - CMP Rated Cable

Pair

Pair Color Code Chart:

Color

Red & Black

Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +150°C
Bulk Cable Weight:	144 lbs/1000 ft.
Max. Recommended Pulling Tension:	365 lbs.
Min. Bend Radius/Minor Axis:	5.250 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	12/01/2011
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL910 Plenum
CSA Flame Test:	FT6

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	1818R

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

 Capacitance (pF/ft)
 31

Nom. Capacitance Cond. to Other Conductor & Shield:

 Capacitance (pF/ft)
 56

Nominal Velocity of Propagation:

 VP (%)
 66

Nom. Conductor DC Resistance:

 DCR @ 20°C (Ohm/1000 ft)
 14.8

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 10.800 Ohm/1000 ft

Max. Operating Voltage - UL:

 Voltage
 300 V RMS

Max. Recommended Current:

 Current
 1.45 Amps per conductor @ 25°C

Notes (Overall)

Notes: Pair jackets and shields are bonded so both strip simultaneously with automatic stripping equipment. Beldfoil® provides high reliability with ease of termination.

1818P Multi-Conductor - CMP Rated Cable

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1818P 0101000	1,000 FT	152.000 LB	BLACK	C	12 FS PR #22 FEP SLF SLF
1818P 010500	500 FT	82.000 LB	BLACK		12 FS PR #22 FEP SLF SLF

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 0 Revision Date: 12-16-2011

© 2015 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.