

Building Entrance Terminals

INDOOR - MS2 CONNECTOR SERIES - BET

1890ECM1-100

100 PAIR - INDOOR BET - MS2/66 - COVER & SPLICE CHAMBER



Product Specifications

UL497 Primary Protector for Communication Circuits

NAFTA Country of Origin: CANADA - All Models are "Buy America Act" Approved.

These 16 AWG steel building entrance terminals feature an easy to install MS2 style connector for use in specialized OSP installations including ONU and FTTx and military command and control centers. Also included are multiple external and internal ground lugs as well as a splice chamber. UL Approval standard on all terminals. Standard 5-pin protector modules, available in gas tube and solid state versions, are sold separately.

Features & Benefits

- 16 AWG Powder Coated Steel Construction
- Equipped with an Internal 26 AWG Fuse Link
- External Ground Connectors Accept 6 14 AWG Wire
- Industry Standard 5 Pin Design
- Exceeds UL497 Primary Protection Standards
- Stackable with Connection Grommets Included
- MS2 Input Accepts 22 28 AWG Wire/66 Output Accepts 22- 26 AWG Wire



1890ECM1-100

Ordering Information

Model Number	Stock Code	Pair Count	Input	Output	Dimensions (H" x W" x D")	Weight (lbs)
1890ECM1-100	134031	100	MS2	66	12.00 x 19.00 x 4.50	26

Circa Telecom, Inc ® 2013 - Version 1.03



Building Entrance Terminals

INDOOR - MS2 CONNECTOR SERIES - BET

1890ECM1-100


100 PAIR - INDOOR BET - MS2/66 - COVER & SPLICE CHAMBER




Physical Dimensions

UL497 Primary Protector for Communication Circuits

12.00 x 19.00 x 4.50 (H" x W" x D")





Notes

Installation:

Indoor Wall Mount

MS2 Connector Input - 3.5' 24 AWG Cable Stub

Splice Chamber: Separate enclosure and cover for OPS gel filled Input cable RUS Approved Material - 2011 Edition RUS Publication 344-2 (Section 4.1.2 and 4.2)

Circa Telecom, Inc ® 2013 - Version 1.03