



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS.
3. RAIL ADJUSTMENTS MEASUREMENTS ARE TAKEN FROM THE FRONT FACE OF EACH EQUIPMENT RAIL. INDEPENDENT ADJUSTABLE REAR EQUIPMENT MOUNTING RAILS (EIA) ADJUST FROM 141mm [5.5in] TO 437mm [17.2in] AND FROM 526mm [20.7in] TO 933mm [36.7in] WITH PDU BRACKETS AND CABLE MANAGEMENT FINGERS IN PLACE.
4. CAN BE USED WITH ANY 19" EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
5. EIA UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS 15.88mm [.625in], 15.88mm [.625in], 12.70mm [.5in], 15.88mm [.625in], 15.88mm [.625in], 12.7mm [.5in]...ETC.
6. PARTS SUPPLIED:
 - BASE CABINET
 - FRONT PERFORATED SINGLE HINGE DOOR (SEE CHART ON SHEET 2)
 - REAR PERFORATED SPLIT DOOR (SEE CHART ON SHEET 2)
 - EQUIPMENT RAILS FRONT & REAR (SEE CHART ON SHEET 2)
 - PDU BRACKETS (SEE CHART ON SHEET 2)
 - CASTERS (SEE CHART ON SHEET 2)
 - INSTRUCTION SHEET
7. RACK UNIT SPACING NUMERALS ARE CLEARLY PRINTED ON EQUIPMENT MOUNTING RAILS.
8. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
9. STATIC LOAD RATING. 1360 Kg (3000 LBS)
10. ROLLING LOAD RATING. 1133 Kg (2500 LBS)
11. SINGLE POINT GROUND LOCATIONS AT TOP AND BOTTOM OF CABINET.
12. ALL CABINET RAILS ARE INSTALLED NUMBERS UP.
13. MAXIMUM EQUIPMENT DEPTH, 959mm [37.75].

01A	11-13-14	PBS	ADP	TCN	FLOOR MOUNT DIMENSIONS UPDATED	V09000BX	
00B	5-13-13	MDCA	JDW	JDWE	REVISED CHART	12V305TL-DC	
00A	8-29-12	TWV	JDW	PBD	RELEASED TO PRODUCTION	12V305TL-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

TITLE				NET-ACCESS S TYPE CABINET 800mm WIDE X 1070mm DEEP FAMILY	
				CUSTOMER DRAWING	
ITEM REVISION NAME					
12V305TL/01.PRT					
DATASET FILE NAME				MATERIAL :	
12V305TL_DC/01A.PRT					
 THIRD ANGLE PROJECTION				N/A	
				DRAWING NUMBER:	
				12V305TL -DC	
DRAWN BY	DATE	CHK	SCALE	SIZE	
TWV	8-29-12	JDW	NONE	A	
				SHT 1 OF 5	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	SINGLE HINGE FRONT DOOR	SPLIT REAR DOOR	SPLIT SIDE PANEL	FRONT CAGE NUT E-RAIL	REAR CAGE NUT FINGER MGMT E-RAIL	REAR CAGE NUT VERTICAL PATCH E-RAIL	STANDARD PDU BRACKETS	CASTERS	CABLE MGMT FINGERS	VERTICAL PATCHING	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
S8212*	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1070mm DEEP	01	01	02	02	02	00	02	04	00	00	142 Kg/EACH 315 LBS/EACH	163 Kg/EACH 360 LBS/EACH
S8512*	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1070mm DEEP	01	01	02	02	02	00	02	04	00	00	149 Kg/EACH 330 LBS/EACH	170 Kg/EACH 375 LBS/EACH
S8812*	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1070mm DEEP	01	01	02	02	02	00	02	04	00	00	156 Kg/EACH 345 LBS/EACH	176 Kg/EACH 390 LBS/EACH
S8219*	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1070mm DEEP	01	01	00	02	02	00	02	04	00	00	120 Kg/EACH 265 LBS/EACH	140 Kg/EACH 310 LBS/EACH
S8519*	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1070mm DEEP	01	01	00	02	02	00	02	04	00	00	127 Kg/EACH 280 LBS/EACH	147 Kg/EACH 325 LBS/EACH
S8819*	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1070mm DEEP	01	01	00	02	02	00	02	04	00	00	133 Kg/EACH 295 LBS/EACH	154 Kg/EACH 340 LBS/EACH
S8212*F	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1070mm DEEP	01	01	02	02	02	00	02	04	01	00	143 Kg/EACH 317 LBS/EACH	164 Kg/EACH 362 LBS/EACH
S8512*F	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1070mm DEEP	01	01	02	02	02	00	02	04	01	00	150 Kg/EACH 332 LBS/EACH	171 Kg/EACH 377 LBS/EACH
S8812*F	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1070mm DEEP	01	01	02	02	02	00	02	04	01	00	157 Kg/EACH 347 LBS/EACH	177 Kg/EACH 392 LBS/EACH
S8219*F	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1070mm DEEP	01	01	00	02	02	00	02	04	01	00	121 Kg/EACH 267 LBS/EACH	141 Kg/EACH 312 LBS/EACH
S8519*F	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1070mm DEEP	01	01	00	02	02	00	02	04	01	00	128 Kg/EACH 282 LBS/EACH	148 Kg/EACH 327 LBS/EACH
S8819*F	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1070mm DEEP	01	01	00	02	02	00	02	04	01	00	134 Kg/EACH 297 LBS/EACH	155 Kg/EACH 342 LBS/EACH
S8212*S	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1070mm DEEP	00	00	02	02	02	00	02	04	00	00	118 Kg/EACH 260 LBS/EACH	138 Kg/EACH 305 LBS/EACH
S8512*S	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1070mm DEEP	00	00	02	02	02	00	02	04	00	00	125 Kg/EACH 275 LBS/EACH	145 Kg/EACH 320 LBS/EACH
S8812*S	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1070mm DEEP	00	00	02	02	02	00	02	04	00	00	131 Kg/EACH 290 LBS/EACH	152 Kg/EACH 335 LBS/EACH
S8219*S	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1070mm DEEP	00	00	00	02	02	00	02	04	00	00	97 Kg/EACH 215 LBS/EACH	117 Kg/EACH 260 LBS/EACH
S8519*S	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1070mm DEEP	00	00	00	02	02	00	02	04	00	00	104 Kg/EACH 230 LBS/EACH	124 Kg/EACH 275 LBS/EACH
S8819*S	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1070mm DEEP	00	00	00	02	02	00	02	04	00	00	111 Kg/EACH 245 LBS/EACH	131 Kg/EACH 290 LBS/EACH


* DENOTES COLOR
 "B" = BLACK, "W" = WHITE



							TITLE NET-ACCESS S TYPE CABINET 800mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING					
							ITEM REVISION NAME 12V305TL/01.PRT				PANDUIT	
							DATASET FILE NAME 12V305TL_DC/01A.PRT					
01A	11-13-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	THIRD ANGLE PROJECTION				MATERIAL: N/A	
00B	5-13-13	MDCA	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TL-DC					DRAWING NUMBER: 12V305TL-DC	
00A	8-29-12	TWV	JDW	PBD	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TL-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY TWV	DATE 8-29-12	CHK JDW	SCALE NONE	SHT 2 OF 5	SIZE A

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



							TITLE NET-ACCESS S TYPE CABINET 800mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING					
							ITEM REVISION NAME 12V305TL/01.PRT					
							DATASET FILE NAME 12V305TL_DC/01A.PRT					
							 THIRD ANGLE PROJECTION					
01A	11-13-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	 THIRD ANGLE PROJECTION				MATERIAL: N/A	
00B	5-13-13	MDCA	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TL-DC					DRAWING NUMBER: 12V305TL-DC	
00A	8-29-12	TWV	JDW	PBD	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TL-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY TWV	DATE 8-29-12	CHK JDW	SCALE NONE	SHT 3 OF 5	SIZE A

2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

B

RACK UNITS ARE
NUMBERED AND
INDEXED FOR
IDENTIFICATION

(2) FIXED
FRONT
EQUIPMENT
RAILS



FRONT

REAR

(2) PDU
BRACKETS

SEE NOTES ON
SHEET 1 FOR
REAR EQUIPMENT
RAIL ADJUSTMENT
RANGE


VERTICAL CABLE
MANAGEMENT FINGERS
WITH BEND RADIUS
CONTROL CAN BE ASSEMBLED
TO CABLE MANAGEMENT TYPE
RAILS BY CUSTOMER
(NOT SHOWN)

(2) REAR EQUIPMENT
RAILS EITHER
CABLE MANAGEMENT TYPE
-OR-
VERTICAL PATCH TYPE
SEE P/N REFERENCE TABLE
ON SHEET 2 FOR CABINET
CONFIGURATIONS

(6) LOCATIONS
TAPPED FOR M10
THREADED ROD

REAR

(2) 165mm X 165mm
[6.5in] [6.5in]
KNOCKOUTS FOR PDU
POWER CORDS
COMPATIBLE
W/ COOL BOOT
P/N: CTGN6X6



FRONT

TOP VIEW


(12) CABLE
OPENINGS
(83mm X 120mm)
[3.26in] [4.7in]
WITH BEZELS
AND COVERS
COMPATIBLE
W/ COOL BOOT
P/N: CTGN3X5

B


FRONT DOOR, REAR DOOR,
AND SIDE PANELS NOT SHOWN

A

01A	11-13-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	
00B	5-13-13	MDCA	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TL-DC	
00A	8-29-12	TWV	JDW	PBD	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TL-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

TITLE					NET-ACCESS S TYPE CABINET 800mm WIDE X 1070mm DEEP FAMILY				
					CUSTOMER DRAWING				
ITEM REVISION NAME									
12V305TL/01.PRT									
DATASET FILE NAME					MATERIAL:				
12V305TL_DC/01A.PRT									
 THIRD ANGLE PROJECTION					N/A				
					DRAWING NUMBER:				
					12V305TL - DC				
DRAWN BY		DATE		CHK		SCALE		SIZE	
TWV		8-29-12		JDW		NONE		SHT 4 OF 5	
					A				

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



REAR OF CABINET
BOTTOM VIEW

FLOOR MOUNTING HOLE LOCATIONS -
SOME PARTS REMOVED FOR CLARITY

TITLE
NET-ACCESS S TYPE CABINET
800mm WIDE X 1070mm DEEP FAMILY
CUSTOMER DRAWING

ITEM REVISION NAME
12V305TL/01.PRT

DATASET FILE NAME
12V305TL_DC/01A.PRT


PANDUIT

MATERIAL:

N/A

DRAWING NUMBER:

12V305TL-DC



THIRD ANGLE
PROJECTION

DRAWN BY	DATE	CHK	SCALE	SHT 5 OF 5	SIZE
TWV	8-29-12	JDW	NONE		A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01A	11-13-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX
00B	5-13-13	MDCA	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TL-DC
00A	8-29-12	TWV	JDW	PBD	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TL-DC