

1890ECT1-100

100 PAIR - INDOOR BET - 66/66 - COVER & SPLICE CHAMBER

Product Specifications

UL497 Primary Protector for Communication Circuits

NAFTA Country of Origin: CANADA - All Models are "Buy America Act" Approved.

These 16 AWG steel building entrance terminals feature reliable 66 block style Quick Clip connectors for both input and output terminals. Connectors can accept up to an 18 AWG line termination. Also included are multiple external and internal ground lugs. UL Approval standard on all terminals. Standard 5-pin protector modules, available in gas tube, solid state and hybrid versions, can be purchased separately. Call for more detailed information on RDUP/RUS-listed units.

Features & Benefits

- 16 AWG Powder Coated Steel Construction
- Equipped with an Internal 26 AWG Fuse Link
- External Ground Connectors Accept 6 - 14 AWG Wire
- Industry Standard 5 Pin Design
- Exceeds UL497 Primary Protection Standards
- Stackable with Connection Grommets Included
- 66 Block Accepts 22 - 26 AWG Wire/18 - 19 AWG Stripped Solid Copper Wire



1890ECT1-100

Ordering Information

Model Number	Stock Code	Pair Count	Input	Output	Dimensions (H" x W" x D")	Weight (lbs)
1890ECT1-100	133030	100	66	66	11.70 x 19.00 x 4.48	27



Building Entrance Terminals

INDOOR - 66 BLOCK SERIES - BET

1890ECT1-100


100 PAIR - INDOOR BET - 66/66 - COVER & SPLICE CHAMBER



Physical Dimensions

UL497 Primary Protector for Communication Circuits

11.70 x 19.00 x 4.48
(H" x W" x D")



Notes

Installation:

Indoor Wall Mount

Splice Chamber: Separate enclosure and cover for OPS gel filled Input cable
RUS Approved Material - 2011 Edition RUS Publication 344-2 (Section 4.1.2 and 4.2)

Circa Telecom, Inc © 2013 - Version 1.03

6914 W. Linebaugh Ave - Tampa, FL 33625
Phone 800.783.6556 - Fax 813.676.2060 - Email circatech@circa telecom.com - www.circa telecom.com