

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
VB1A1P3BN24E1	17 lb (7.7 kg)




NOTES:

1. IDENTIFICATION: VERTICAL, (24) 5-20R, METERED
120V / 30A / THREE-PHASE WYE POU

<u>PART NO.</u>	<u>COLOR</u>
VB1A1P3BN24E1	BLACK

2. ACCESSORY COMPONENTS:
 (4) #10-32 x 1/2" MOUNTING SCREWS
 (4) #12-24 x 1/2" MOUNTING SCREWS
 (2) #10-32 LOCKING COLLAR SCREWS
 (2) L-BRACKETS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).
4. CURRENT METER - RED, 4-DIGIT LED DISPLAY PROVIDES TRUE RMS CURRENT THAT CONTINUOUSLY SCROLLS THROUGH THE THREE DIFFERENT MEASURED CIRCUITS. METER DISPLAYS CIRCUIT NAME FOLLOWED BY THE MEASURED CURRENT (E.G. CR-1 REPRESENTS PHASE 1).
5. RECEPTACLES ARE COLOR CODED PER PHASE FOR EASY IDENTIFICATION AND LOAD BALANCING.
6. UL® & c-UL® LISTED 60950.
7. RoHS COMPLIANT.
8. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
9. MAXIMUM AVAILABLE INPUT POWER = 8.6 KW
10. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



01A	8-7-12	PIP	MRWA	B. UPDATED NOTE #9. C. ADDED NOTE #10.	09V098EE					
00B	1-31-11	MAV	KRKE	A. ADDED MAXIMUM AVAILABLE POWER	09V098EE					
00A	10-15-10	MAV	KRKE	RELEASED TO PRODUCTION	09V098EE					
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH		

MODEL FILENAME		09V098EE/01.PRT	
CAD FILENAME/LAYERS		09V098EE_DC/01A.PRT	
PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, (24) 5-20R, METERED POWER OUTLET UNIT (VB1A1P3BN24E1) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES [METRIC - MILLIMETER] ANGLE X.X +/- 0.03 X, +/- 0.8 X.XX +/- 0.015 X.X +/- 0.4 +/- 1° X.XXX +/- 0.005 X.XX +/- 0.13		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY MAV		SCALE NONE	
DATE 10-15-10		DRAWING NO. 09V098EE	
CHK'D KRKE		DWG B	