



## Building Entrance Terminals

HIGH SPEED DATA - INDOOR - 66 BLOCK SERIES - BET



### 2606QC/QCe

4 - 6 PAIR - CAT5e - INDOOR BET - 66/66 - NO COVER

#### Product Specifications


### UL497 Primary Protector for Communication Circuits

NAFTA Country of Origin: CANADA - All Models are "Buy America Act" Approved.

The Enhanced Series is built to be a universal protector with throughput of up to 1Gbps and clamping speeds of 2-3 nanoseconds. Available in 66 block, 110 connector or BIX. Select the right voltage and protect everything from VOIP to networks, digital phones to VDSL2.

## Features & Benefits

- Certified Category 5e
- 16 AWG Powder Coated Steel Construction
- Equipped with an Internal 26 AWG Fuse Link
- External Ground Connectors Accept 6 - 14 AWG Wire
- Industry Standard 5 Pin Design
- Exceeds UL497 Primary Protection Standards
- 66 Block Accepts 22 - 26 AWG Wire/18 - 19 AWG Stripped Solid Copper Wire



2606QC/QCe

#### Ordering Information

Model Number	Stock Code	Pair Count	Input	Output	Dimensions (H" x W" x D")	Weight (lbs)
2606QC/QCe	123113	6	66	66	4.50 x 3.50 x 2.69	1.5



## Building Entrance Terminals

HIGH SPEED DATA - INDOOR - 66 BLOCK SERIES - BET




### 2606QC/QCe

4 - 6 PAIR - CAT5e - INDOOR BET - 66/66 - NO COVER

#### Physical Dimensions

### UL497 Primary Protector for Communication Circuits

4.50 x 3.50 x 2.69  
(H" x W" x D")



#### Notes

Installation: Indoor Wall Mount

When used in conjunction with the Circa Telecom CAT5e/Hybrid Module Series

Additional two pair can be left open or used for standard voice lines.