



Building Entrance Terminals

INDOOR - 66 BLOCK SERIES - BET



2612QC/QC

12 PAIR - INDOOR BET - 66/66 - NO COVER

Product Specifications


UL497 Primary Protector for Communication Circuits

NAFTA Country of Origin: CANADA - All Models are "Buy America Act" Approved.

These 16 AWG steel building entrance terminals feature reliable 66 block style Quick Clip connectors for both input and output terminals. Connectors can accept up to an 18 AWG line termination. Also included are multiple external and internal ground lugs. UL Approval standard on all terminals. Standard 5-pin protector modules, available in gas tube, solid state and hybrid versions, can be purchased separately. Call for more detailed information on RDUP/RUS-listed units.

Features & Benefits

- 16 AWG Powder Coated Steel Construction
- Equipped with an Internal 26 AWG Fuse Link
- External Ground Connectors Accept 6 - 14 AWG Wire
- Industry Standard 5 Pin Design
- Exceeds UL497 Primary Protection Standards
- 66 Block Accepts 22 - 26 AWG Wire/18 - 19 AWG Stripped Solid Copper Wire



2612QC/QC

Ordering Information

Model Number	Stock Code	Pair Count	Input	Output	Dimensions (H" x W" x D")	Weight (lbs)
2612QC/QC	104003	12	66	66	10.00 x 4.50 x 2.75	2.5



Building Entrance Terminals

INDOOR - 66 BLOCK SERIES - BET

2612QC/QC



12 PAIR - INDOOR BET - 66/66 - NO COVER



Physical Dimensions

UL497 Primary Protector for Communication Circuits

10.00 x 4.50 x 2.75
(H" x W" x D")



Notes

Installation:

Indoor Wall Mount

RUS Approved Material - 2011 Edition RUS Publication 344-2 (Section 4.1.2 and 4.2)

Circa Telecom, Inc © 2013 - Version 1.03

6914 W. Linebaugh Ave - Tampa, FL 33625
Phone 800.783.6556 - Fax 813.676.2060 - Email circatech@circa telecom.com - www.circa telecom.com