



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:


1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. PART CAN BE INSTALLED INTO "ROUND" OR "RECTANGULAR" PUNCHOUTS IN STEEL STUDS WITH MATERIAL THICKNESS UP TO 0.080".
3. PART SUITABLE FOR USE IN HOLES PUNCHED WITH PANDUIT PART #MSPT-1,3.
4. ANTI-VIBRATION TABS ARE INTENDED FOR USE WITH CONDUIT, OR PIPE, FROM 1/2" TO 1" OD.




RECTANGULAR SIDE




ROUND SIDE



ANTI-VIBRATION TABS




ISOMETRIC VIEW
SCALE 1:2




SECTION A-A

APPLICABLE PUNCHOUT
SHAPES (SCALE 3:4)



ROUND
PUNCHOUT

- MINIMUM LENGTH
OF STRAIGHT,
PARALLEL EDGES



RECTANGULAR PUNCHOUTS

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G03677BF_DC_GB3677BF/05A

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

MSGV - 1.3

METAL STUD GROMMET w/ ANTI-VIBRATION

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

AWN BY

ARHA

MAT'L:
POLYPROPYLENE
(YELLOW)

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE
PROJECTION.

SCALE

— 28 —

DRAWING NO.

GB3677BF

A

05A	12/07/09	ARHA	<i>gjn</i>	INITIAL RELEASE	GB3677BF	05A	<i>ken</i>			
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP			