


1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6) C-19 NETWORKED
230/400V / 20A / THREE-PHASE WYE POU



PANDUIT P/N	WEIGHT
QZ1D1K0BA30P1	17 lb (7.7 kg)

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).

8. MAXIMUM AVAILABLE POWER = 11 KW




TOOLLESS MOUNTING BUTTON LOCATION




— 10 FOOT INLET POWER CORD



PLUG
20 AMP, 230/400V x 3~ WYE
TWIST LOCK
NEMA L22-20P



TWENTY-FOUR (24)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13



SIX (6)
RECEPTACLES
20 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

00A	11-22-10	MAV	KRRE	RELEASED TO PRODUCTION	09V098NP				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	

MODEL FILENAME		09V098NP/00.PRT	
CAD FILENAME/LAYERS		09V098NP_DC/00A.PRT	
<div style="font-size: 48px; font-family: sans-serif; letter-spacing: 10px;">PANDUIT</div> <div style="font-size: 24px; font-weight: bold; margin-top: 5px;">CORP</div> <div style="font-size: 18px; margin-top: 5px;">TINLEY PARK, ILLINOIS</div>			
VERTICAL, MIXED (24) C-13 & (6) C-19 NETWORKED POWER OUTLET UNIT (QZ1D1K0BA30P1) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
[METRIC - MILLIMETER] X. +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13		ANGLE +/- 1°	
DRAWN BY <div style="font-size: 24px; font-weight: bold;">MAV</div>		SCALE <div style="font-size: 24px; font-weight: bold;">NONE</div>	
DATE <div style="font-size: 24px;">11-22-10</div>		DRAWING NO. <div style="font-size: 24px; font-weight: bold;">09V098NP</div>	
CHK'D <div style="font-size: 24px; font-family: cursive;">KRKE</div>		DWG <div style="font-size: 24px; font-weight: bold;">B</div>	