

LC Uniboot to SC Duplex, 2 F, Interconnect Cable, Riser

FRNC, single-mode (OS2), 4 m

CORNING

Pretium EDGE® Solutions jumpers are integrated reverse-polarity uniboot duplex assemblies that meet the high-density space requirements of the MDA and EDA and provide a 50-percent reduction in bulk cabling when compared to traditional duplex jumpers. The highly flexible, 2-fibre interconnect cable reduces cable congestion, improves jumper management and routing and improves air circulation.

Enabled by Corning® ClearCurve® multimode optical fibre, Pretium EDGE® Solutions jumpers feature ultra-bendable performance and accommodate a minimum bend-radius of 10 mm with minimal bend-induced attenuation loss. With this bend performance, Pretium EDGE Solutions jumpers can greatly reduce outages and degradation in systems caused by severe bending problems.

Additional detailed furcation images are available in the Cable Assembly Family Specification Sheet.



Features and Benefits

Factory-terminated solutions

Provide consistent quality, ensure system performance, and reduce installation time

Low insertion loss performance

Allows for more connections in a link when deploying a TIA-942-compliant system

Specifications

General Specifications

Application	Data Centre, FRNC, General building applications
Cable type	FRNC
Cable assembly type	Two Fibre
Fibre category	single-mode (OS2)

Design - Connector A

Connector type	LC Uniboot
Ferrule Material	Ceramic
Housing material	Composite
Housing colour	black
Boot colour	turquoise

LC Uniboot to SC Duplex, 2 F, Interconnect Cable, Riser

FRNC, single-mode (OS2), 4 m

CORNING

Design - Connector B

Connector type	SC duplex
Ferrule Material	Ceramic
Housing material	Composite
Housing colour	black
Boot colour	turquoise

Cable design

Fibre count	2
Outer jacket colour	turquoise

Mechanical Characteristics Cable

Nominal Outer Diameter	2 mm (0.08 in)
------------------------	----------------

Mechanical Characteristics - Furcation Leg

Minimum Bend Radius	10 mm
---------------------	-------

Chemical characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Fibre Specifications

Optical Characteristics (cabled)

Fibre Name	E9/125 SMF28e+
Fibre Core Diameter	8.2 µm
Fibre category	OS2
Fibre Code	E
Wavelengths	1310 nm / 1383 nm / 1550 nm
Maximum Attenuation	0.36 dB/km / 0.36 dB/km / 0.22 dB/km

Notes: 1) Meets 0.75 ns optical skew when used in all Corning Plug and Play™/Pretium EDGE® systems solutions.
2) Improved attenuation and bandwidth options available
3) Bend-insensitive single-mode fibres available on request
4) Contact a Corning Customer Care Representative for additional information

LC Uniboot to SC Duplex, 2 F, Interconnect Cable, Riser

FRNC, single-mode (OS2), 4 m

CORNING

Fibre Specifications

Optical Characteristics (cabled)	
Serial 1 Gigabit Ethernet	5000 m / - / -
Serial 10 Gigabit Ethernet	10000 m / - / 40000 m
Cable cutoff wavelength	1260 nm

Notes: 1) Meets 0.75 ns optical skew when used in all Corning Plug and Play™/Pretium EDGE® systems solutions.
2) Improved attenuation and bandwidth options available
3) Bend-insensitive single-mode fibres available on request
4) Contact a Corning Customer Care Representative for additional information

Ordering Information

Part Number	727802GNZ20004M
Product Description	LC Uniboot to SC Duplex, 2 fibres, Interconnect Cable, Riser, FRNC, single-mode (OS2), 4 m
EAN Code	4042673583974
Length	4 m

Shipping Information

Units per delivery	1/1
--------------------	-----



Corning Optical Communications GmbH & Co. KG · Leipziger Strasse 121 · 10117 Berlin, GERMANY
00 800 2676 4641 · FAX: +49 30 5303 2335 · www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2015 Corning Optical Communications. All rights reserved.