

NOTES:
1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6)C-19, METERED
120V / 30A / THREE-PHASE WYE POU

<u>PART NO.</u>	<u>COLOR</u>
VB1A1P3BN30P1	BLACK

- A**







Diagram illustrating the dimensions and reference point for the 2x2 grid of cells. The grid is composed of four cells, each measuring 2.0 (50.8) REF in width and height. The total width of the grid is 3.44 (87.4) REF. The reference point is located at the top-left corner of the grid.

— 10 FOOT INLET POWER CORD



MODEL FILENAME		09V098EM/00.PRT	
CAD FILENAME/LAYERS		09V098EM_DC/00B.PRT	
PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, MIXED (24) C-13 & (6) C-19, METERED POWER OUTLET UNIT (VB1A1P3BN30P1) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		[METRIC - MILLIMETER] X. +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13	
ANGLE +/- 1°		ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY MAV		SCALE NONE	
DATE 10-15-10		DRAWING NO. 09V098EM	
CHK'D KRKE		DWG B SIZE	