

Leading the Way in Megapixel Video™

Surround Video® Omni IP Megapixel Cameras

12MP WDR or 20MP H.264 All-in-One Omni-Directional User-Configurable Multi-Sensor True Day/Night Indoor/Outdoor Dome IP Cameras



Multi-Sensor Omni

Camera Models

12 Megapixel	20 Megapixel
AV12176DN-NL	AV20175DN-NL
AV12176DN-28	AV20175DN-28
AV12176DN-08	AV20175DN-08

Description:

Delivering revolutionary flexibility, Arecont Vision SurroundVideo® Omni multi-sensor, multi-megapixel cameras provide ample resolution to zoom-in for details in live and recorded video. With multiple imagers, each with a choice of an IR corrected lens, one SurroundVideo® Omni can replace 4 standard cameras, requiring just a single installation with only one ethernet cable.

A unique track design allows four individual sensor gimbals to be independently placed in nearly any configuration. Popular uses of SurroundVideo® Omni IP66 rated / IK-10 impact-resistant cameras are to

cover the intersection of hallways or to provide a 270° view at the corner of a building.

SurroundVideo® Omni cameras are available in total resolutions of 12 megapixels (MP) or 20 megapixels. Optional lenses can be selected from a choice of 2.8, 4, 6, 8, 12 and 16mm. Wide Dynamic Rage (WDR) that delivers up to 100dB at full resolution is available in the 12MP model. H.264 compression reduces bandwidth and storage requirements, while delivering full frame rates and resolution, without sacrificing image quality.



Omni-Directional Track with



270° FOV



Wide Dynamic Range on 12MP Models



True Day/Night with IR Cut Filter



Pixel Binning Mode



Dual Encoder



Ultra Low Profile



Impact / Weather Resistant IK-10 and IP66 Rated

Features:

- 12MP WDR and 20MP Configurations
- Up to 4 Individual Camera Gimbals can be Independently Placed in Any Orientation Around a 360° Track with Extra Positions for Looking Straight Down
- Multiple Lens Options in a Single Camera Housing from 2.8mm up to 16mm
- True WDR up to 100dB at Full Resolution: See Clearly in Shaded and Bright Light Conditions Simultaneously
- True Day/Night Functionality with Mechanical IR Cut Filter
- · Binning Mode for Strong Low Light Performance
- Forensic Zooming Zoom Live or After the Event While Recording Full Field-of-View in HD – Replace PTZ Devices
- Fast Frame Rates
- Privacy Mask, Motion Detection, Flexible Cropping, Bit Rate Control and Multi-Streaming
- Dual Encoder H.264/MJPEG
- PoE and Auxiliary Power: 12-48V DC/24V AC
- · Ultra Discrete, Low-Profile Housing
- · Outdoor Rated IP66 and IK-10 Impact-Resistant Housing
- · Complete Mounting Options
- · Reduced Overall System Cost

Model Specific Features


Model	Resolution	Resolution Frame Rate		Features		
AV12176DN-NL	12MP	5.2fps	WDR	Binning		
AV12176DN-28	12MP	5.2fps	WDR	Binning		
AV12176DN-08	12MP	5.2fps	WDR	Binning		
AV20175DN-NL	20MP	3.5fps		Binning		
AV20175DN-28	20MP	3.5fps		Binning		
AV20175DN-08	20MP	3.5fps		Binning		

Options

-NL	No Lenses (User Configurable and Ordered Separately)
-28	Configured with 2.8mm Lenses*
-08	Configured with 8mm Lenses**

- * Good option for a 270° Corner Mount configuration
- ** Good configuration option for a hallway intersection





Camera Imaging

Model			AV12176DN	AV20175DN		
Image Sensor		4 x 3MP CMOS		4 x 5MP CMOS		
Optical Format		1/3.2"		1/2.5"		
Pixel Pitch		2.2µm			2.2µm	
Minimum II	lumination	Color	0.5 Lux	Color	0.3 Lux	
		Color Binning	0.15 Lux	Color Binning	0.15 Lux	
		Day/Night	0 Lux, IR sensitive	Day/Night	0 Lux, IR sensitive	
Full Field of View (FOV) Resolution 1/4 Resolution		Total	8192 H x 1536 V	Total	10240 H x 1920 V	
		Per Sensor	2048 H x 1536 V	Per Sensor	2560 H x 1920 V	
		Total	4096 H x 768 V	Total	5120 H x 960 V	
		Per Sensor	1024 H x 768 V	Per Sensor	1280 H x 960 V	
Dynamic R	ange	Up to 100dB at Full Resolution		70.1dB		
Lens	2.8mm Lens Option (-28 Models)	2.8	mm, F/1.8", H-FOV = 89°	2.8mm, F/1.8", H-FOV = 113°		
8mm Lens Option (-08 Models)		8mm, F/1.6", H-FOV = 33°		8mm, F/1.6", H-FOV = 40°		
Video Frame Rates		Max 5.2fps (8192 x 1536)		Max 3.5fps (10240 x 1920)		
		16.7fps (4096 x 768)		11fps (5120 x 960)		

Data Transmission

Compression Type	H.264 (MPEG-4, Part 10)/Motion JPEG
	21 levels of quality
Network Protocols	RTSP, RTP/TCP, RTP/UDP, HTTP, DHCP, TFTP
Network Interface	100Base-T Ethernet
Multi-Streaming	8 non-identical streams (2 per sensor)

Electrical

Input/Output	General purpose opto-coupled
Power Over Ethernet	PoE 802.3af, Class 3
Auxiliary Power	12-48V DC and 24V AC
Max Power Consumption	14 Watts Max (Auxiliary Power)

Programmability

Auto adjustment between WDR and LDR modes (12MP Models)	
Binning Mode	
Privacy mask	
Flexible Cropping (resolution windowing down to 1x1 pixel for JPEG and 2x2 pixels for H.264)	l
Auto Exposure (AE) and Gain Control (AGC) > 120dB	
On-camera real-time motion detection with up to 1024 detection zones (per sensor)	
Auto multi-matrix white balance	
50/60Hz selectable flicker control	
Electronic pan, tilt, zoom (PTZ)	
Programmable shutter speed to help control motion blur	
MoonLight™ Mode: extended exposure and proprietary noise cancellation	n
Programmable resolution, brightness, saturation, gamma, sharpness, tin	t
Simultaneous delivery of full field-of-view and zoomed images	
Bandwidth and storage savings by running at 1/4 resolution	
Bit rate and bandwidth limit control	


Mechanical

Casing	Die-cast aluminum chassis with polycarbonate dome bubble			
	IP66 weather proof standard			
	Impact resistant, IK-10 rated			
Gimbal	Easily adjustable, 2-axis w/360° pan and 90° tilt			
Total Unit	Unit	Ø 7.7" (196mm) x 3.1" H (78.5mm)		
Dimensions	Bubble Only	Ø 6.7" (169.2mm) x 1.3" H (33.4mm)		
Weight	Unit	2.8lbs (1.27kg)		
	Packaged	3.4lbs (1.54kg)		

Compliance

Industry Standard	ONVIF Profile S Conformant
Listings	UL (CB)
FCC Compliance	47 CFR 15 Class A
Environmental	RoHS, REACH, WEEE

3.1° (78.5 mm) (168.2 mm)



Environmental

Protection Ratings	IP66 water/dust protection rating
	IK-10 impact-resistant polycarbonate dome
Operating temperature	-40°C (-40°F) to +50°C (122°F)
Humidity	0% to 90% (non-condensing)
Stable image temperature	0°C (32°F) to +50°C (122°F)
Storage temperature	-40°C (-40°F) to +60°C (140°F)

Lens Options


Focal Length		2.8mm	4mm	6mm	8mm	12mm	16mm
F Stop		F1.8	F1.6	F1.6	F1.6	F1.6	F1.6
Horiz.	3MP WDR	89	63	43	33	22	16
FOV	5MP	113	80	55	40	28	20
Option		Standard (-28 Models)	Ordered Separately	Ordered Separately	Standard (-08 Models)	Ordered Separately	Ordered Separately
Part Number		MPM2.8	MPM4.0	MPM6.0	MPM8.0	MPM12.0	MPM16.0






Accessories


SO-CAP	Cap for SurroundVideo® Omni
AV-WMJB	Wall Mount Bracket with Junction Box
AV-PMJB	Pendant Mount Bracket with Junction Box
AV-PMA	Pole Mount Adapter
AV-CRMA	Corner Mount Adapter
SV-EBA	Electrical Box Adapter




Ceiling Mount Configuration



Wall Mount Configuration with Pole Mount Adapter



Wall Mount Configuration



Wall Mount Configuration with Corner Mount Adapter

