



Broadband Solutions
SWVPWF81GA
Wall Plate, white, with F81 barrel splice

Environmental Specifications

Safety Standard	CE EN 60728-4 SCTE
-----------------	------------------------

Electrical Specifications

Impedance	75 ohm
Operating Frequency Band	0 – 3000 MHz
Insertion Loss at Frequency Band, maximum	0.2 dB @ 0–1002 MHz 0.3 dB @ 1002–3000 MHz
Return Loss at Frequency Band, minimum	35 dB @ 0–1002 MHz 25 dB @ 1002–2000 MHz 20 dB @ 2000–3000 MHz
Shielding Effectiveness, minimum	120 dB

General Specifications

Device Type	Wallplate
Brand	HomeConnect®
Color	White
Mounting	Flush

Dimensions

Length	28.19 mm 1.11 in
--------	--------------------

Mechanical Specifications

Material Type	Brass Plastic
Plating	Nickel

Packed Dimensions

Carton Quantity	250
Height	292.10 mm 11.50 in
Length	647.70 mm 25.50 in
Width	254.00 mm 10.00 in
Shipping Weight	9.07 kg 20.00 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

SVWPWF81GA

ISO 9001:2008 Designed, manufactured and/or distributed under this quality management system

Included Products

SVF81GA — F81 Barrel Splice, sealing surface