



Cable Continuity Tester

Features/Benefits

- Compact size
- One button test results
- Automatic shut off
- 9 volt battery included

Specifications

- Tests up to 320 feet
- Built-in BNC connector with F connector
- Coax cable types tested: 50-75Ohm RG58, RG59, RG6, RG6 quad, Belden® 8281, RG8 AND RG11

Contents: main and remote continuity test units, 2 F-connector adapters, 2 RJ45 shielded patch cables, 2 belt clips

Description

Catalog No.

Cable continuity tester

TCT2



Tool Kit, 3-Piece

Features/Benefits

- Punch-down tool with 110 and 66 blades and rubber-embedded handle
- Durable, black, nylon belt pouch
- Belt pouch fits up to 3" belt

Specifications

- Punch-down tool for 28-22 AWG solid or stranded wire; twist and lock 110 and 66 blades

Contents: 1 punch-down tool with 110 and 66 blade, 1 pair snips, and 1 belt pouch

Description

Catalog No.

Tool kit, 3-piece

TK3



Tool Kit, 8-Piece

Features/Benefits

- Punch-down tool with 110 and 66 blades; and rubber-embedded handle
- Durable, black, nylon belt pouch
- Belt pouch fits up to 2½" belt (slide on style)

Specifications

- Punch-down tool for 28-22 AWG solid or stranded wire; twist and lock 110 and 66 blades
- Screwdriver:
 - #4 and #6 slotted
 - #2 and #3 Philips bits
- Stripper works on UTP and STP cables
- Snap-X has removable lanyard

Contents: 1 punch-down tool, 110 blade, 66 blade, snips, 4-bit screwdriver, UTP/STP cable stripper/cutter, Maglite™, Belt pouch, and Snap-X termination aid

Description

Catalog No.

Tool kit, 8-piece

TK8



Belden® is a registered trademark of Belden Networking, Inc. Maglite™ is a trademark of Mag Instruments, Inc.