



SAFETY DATA SHEET

ADESCO NUTLOCK 50ML

Page: 1

Compilation date: 10/02/2015

Revision No: 8

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: ADESCO NUTLOCK 50ML

Product code: ASADAN1M500904

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC1: Adhesives, sealants.

1.3. Details of the supplier of the safety data sheet

Company name: Anixter

3 Edmund Road

Sheffield

S2 4EB

England

Tel: 01142 709338

Fax: 01142 709358

Email: gregg.walker@anixter.com

1.4. Emergency telephone number

Emergency tel: 01142 709338

(office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Aquatic Acute 1: H400; Aquatic Chronic 2: H411; Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317; STOT SE 3: H335; -: EUH208

Most important adverse effects: Contains 1-acetyl-2-phenylhydrazine. May produce an allergic reaction. Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation. May cause respiratory irritation. Very toxic to aquatic life. Toxic to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: EUH208: Contains 1-acetyl-2-phenylhydrazine. May produce an allergic reaction.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H335: May cause respiratory irritation.

H400: Very toxic to aquatic life.

H411: Toxic to aquatic life with long lasting effects.

[cont...]

SAFETY DATA SHEET

ADESCO NUTLOCK 50ML

Page: 2

Hazard pictograms: GHS07: Exclamation mark

GHS09: Environmental



Signal words: Warning

Precautionary statements: P261: Avoid breathing vapours.

P264: Wash contaminated skin thoroughly after handling.

P271: Use only outdoors or in a well-ventilated area.

P273: Avoid release to the environment.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P321: Specific treatment (see information on this label).

P302+352: IF ON SKIN: Wash with plenty of water/.

P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P312: Call a POISON CENTER/doctor//if you feel unwell.

P332+313: If skin irritation occurs: Get medical advice/attention.

P337+313: If eye irritation persists: Get medical advice/attention.

P403+233: Store in a well-ventilated place. Keep container tightly closed.

P501: Dispose of contents/container to comply with Local, National and International regulations.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

POLYGLYCOL DIMETHACRYLATE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
203-652-6	109-16-0	-	Skin Sens. 1: H317	30-50%

BIS(ISOPROPYL)NAPHTHALENE

254-052-6	38640-62-9	-	Aquatic Acute 1: H400; Aquatic Chronic 2: H411	10-30%
-----------	------------	---	--	--------

[cont...]

SAFETY DATA SHEET

ADESCO NUTLOCK 50ML

Page: 3

HYDROXYALKYL METHACRYLATE

248-666-3	27813-02-1	-	STOT SE 3: H335; Eye Irrit. 2: H319; Skin Sens. 1: H317	1-10%
-----------	------------	---	--	-------

CUMENE HYDROPEROXIDE

201-254-7	80-15-9	-	Org. Perox. EF: H242; Acute Tox. 3: H331; Acute Tox. 4: H312; Acute Tox. 4: H302; STOT RE 2: H373; Skin Corr. 1B: H314	1-10%
-----------	---------	---	---	-------

ACRYLIC ACID

201-177-9	79-10-7	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Acute Tox. 4: H312; Acute Tox. 4: H302; Skin Corr. 1A: H314; Aquatic Acute 1: H400	<1%
-----------	---------	---	---	-----

1-ACETYL-2-PHENYLHYDRAZINE

204-055-3	114-83-0	-	Acute Tox. 3: H301+311; Skin Irrit. 2: H315; STOT SE 3: H335; Aquatic Chronic 1: H410; Eye Irrit. 2: H319; Skin Sens. 1B: H317	<1%
-----------	----------	---	---	-----

2,6-DI-TERT-BUTYL-P-CRESOL

204-881-4	128-37-0	-	Aquatic Chronic 1: H410; STOT RE 2: H373; Aquatic Acute 1: H400	<1%
-----------	----------	---	--	-----

N,N-DIMETHYL-P-TOLUIDINE

202-805-4	99-97-8	-	Acute Tox. 3: H331; Acute Tox. 3: H311; Acute Tox. 3: H301; STOT RE 2: H373; Aquatic Chronic 3: H412	<1%
-----------	---------	---	--	-----

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

[cont...]

SAFETY DATA SHEET

ADESCO NUTLOCK 50ML

Page: 4

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. The floor of the storage room must be impermeable to prevent the escape of liquids.

7.3. Specific end use(s)

Specific end use(s): No data available.

[cont...]

SAFETY DATA SHEET

ADESCO NUTLOCK 50ML

Page: 5

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

ACRYLIC ACID

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	30 mg/m ³	60 mg/m ³	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. The floor of the storage room must be impermeable to prevent the escape of liquids.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Blue

Odour: Perceptible odour

Evaporation rate: No data available.

Oxidising: No data available.

Solubility in water: Insoluble

Viscosity: No data available.

Boiling point/range°C: >35

Melting point/range°C: No data available.

Flammability limits %: lower: No data available.

upper: No data available.

Flash point°C: >93

Part.coeff. n-octanol/water: No data available.

Autoflammability°C: No data available.

Vapour pressure: No data available.

Relative density: 1.07

pH: No data available.

VOC g/l: No data available.

9.2. Other information

Other information: No data available.

[cont...]

SAFETY DATA SHEET

ADESCO NUTLOCK 50ML

Page: 6

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

CUMENE HYDROPEROXIDE

ORL	MUS	LDLO	5	gm/kg
ORL	RAT	LD50	382	mg/kg
SCU	RAT	LD50	382	mg/kg

ACRYLIC ACID

IPR	RAT	LD50	22	mg/kg
ORL	MUS	LD50	830	mg/kg
ORL	RAT	LD50	1250	mg/kg
SCU	MUS	LD50	1590	mg/kg

N,N-DIMETHYL-P-TOLUIDINE

IPR	MUS	LD50	212	mg/kg
-----	-----	------	-----	-------

Relevant hazards for substance:

Hazard	Route	Basis
--------	-------	-------

[cont...]

SAFETY DATA SHEET

ADESCO NUTLOCK 50ML

Page: 7

Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	DRM	Hazardous: calculated
STOT-single exposure	INH	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Not biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: Bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Toxic to aquatic organisms. Toxic to soil organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN3082

[cont...]

SAFETY DATA SHEET

ADESCO NUTLOCK 50ML

Page: 8

14.2. UN proper shipping name

Shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.
(BIS(ISOPROPYL)NAPHTHALENE)

14.3. Transport hazard class(es)

Transport class: 9

14.4. Packing group

Packing group: III

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: E

Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: EUH208: Contains <name of sensitising substance>. May produce an allergic reaction.

H226: Flammable liquid and vapour.

H242: Heating may cause a fire.

H301: Toxic if swallowed.

H301+311: Toxic if swallowed or in contact with skin.

H302: Harmful if swallowed.

H311: Toxic in contact with skin.

H312: Harmful in contact with skin.

H314: Causes severe skin burns and eye damage.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H331: Toxic if inhaled.

H332: Harmful if inhaled.

[cont...]

SAFETY DATA SHEET

ADESCO NUTLOCK 50ML

Page: 9

H335: May cause respiratory irritation.

H373: May cause damage to organs <or state all organs affected, if known> through prolonged or repeated exposure <state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard>.

H400: Very toxic to aquatic life.

H410: Very toxic to aquatic life with long lasting effects.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.