



**SAFETY DATA SHEET**  
ADESCO AD150 CYANO 50G

Page: 1

Compilation date: 20/04/2015

Revision No: 3

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** ADESCO AD150 CYANO 50G

**Product code:** ASADCY1G500005

**Synonyms:** SUPER GLUE

ETHYL-2-CYANOACRYLATE ESTER

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**Use of substance / mixture:** Cyanoacrylate adhesive

**1.3. Details of the supplier of the safety data sheet**

**Company name:** Anixter

3 Edmund Road

Sheffield

S2 4EB

England

**Tel:** 01142 709338

**Fax:** 01142 709358

**Email:** [gregg.walker@anixter.com](mailto:gregg.walker@anixter.com)

**1.4. Emergency telephone number**

**Emergency tel:** 01142 709338

(office hours only)

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** STOT SE 3: H335; Eye Irrit. 2: H319; Skin Irrit. 2: H315; -: EUH202

**Most important adverse effects:** Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation. Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

**2.2. Label elements**

**Label elements:**

**Hazard statements:** H315: Causes skin irritation.

H319: Causes serious eye irritation.

H335: May cause respiratory irritation.

EUH202: Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

**Hazard pictograms:** GHS07: Exclamation mark

[cont...]

# SAFETY DATA SHEET

## ADESCO AD150 CYANO 50G

Page: 2



**Signal words:** Warning

**Precautionary statements:** P261: Avoid breathing vapours.  
P264: Wash hands thoroughly after handling.  
P271: Use only outdoors or in a well-ventilated area.  
P280: Wear protective gloves/protective clothing/eye protection/face protection.  
P302+352: IF ON SKIN: Wash with plenty of water/.  
P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.  
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P312: Call a POISON CENTER/doctor//if you feel unwell.  
P332+313: If skin irritation occurs: Get medical advice/attention.  
P337+313: If eye irritation persists: Get medical advice/attention.  
P501: Dispose of contents/container to comply with Local, National and International regulations.

### 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

**Hazardous ingredients:**

ETHYL-2-CYANOACRYLATE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
230-391-5	7085-85-0	-	Eye Irrit. 2: H319; STOT SE 3: H335; Skin Irrit. 2: H315	70-90%

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water. Do not pull bonded skin apart. It may be gently peeled apart using a blunt object such as a spoon, preferably after soaking in warm soapy water. Cyanoacrylate gives off heat on solidification. In rare cases a large drop will generate enough heat to burn. Burns should be treated normally after the adhesive has been removed from the skin. If lips are accidentally stuck together apply warm water to the lips and encourage maximum wetting. Peel or roll lips apart. Do not try to pull the lips apart with direct opposing action.

**Eye contact:** Bathe the eye with running water for 15 minutes. If the eye is bonded closed, release

[cont...]

# SAFETY DATA SHEET

## ADESCO AD150 CYANO 50G

Page: 3

eyelashes with warm water by covering with wet pad. Cyanoacrylate will bond to eye protein and will cause periods of weeping which will help to debond the adhesive. Keep eye covered until debonding is complete. Do not force eye open. Medical advice should be sought in case solid particles of cyanoacrylate trapped behind the eyelid cause any abrasive damage.

**Ingestion:** Wash out mouth with water. Ensure that breathing passages are not obstructed. The product will polymerise immediately in the mouth making it almost impossible to swallow. Saliva will slowly separate the solidified product from the mouth (several hours). Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** Cyanoacrylate will bond to eye protein and will cause periods of weeping which will help to debond the adhesive. In a dry atmosphere, 50% RH, vapours may cause irritation and lachrymatory effect.

**Ingestion:** Cyanoacrylates are considered to have relatively low toxicity. Acute oral LD50 is >5000 mg/kg (rat). It is almost impossible to swallow as it rapidly polymerises in the mouth.

**Inhalation:** In dry atmospheres with <50% humidity, vapours may irritate the eyes and respiratory system. Prolonged exposure to high concentrations of vapours may lead to chronic effects in sensitive individuals.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

### 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Eye bathing equipment should be available on the premises.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Use foam, Carbon Dioxide or dry powder as extinguishing media.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Ensure adequate ventilation Do not use cloths for mopping up.

[cont...]

# SAFETY DATA SHEET

## ADESCO AD150 CYANO 50G

Page: 4

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Polymerise with water and scrape off floor.

### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.  
Do not handle in a confined space. Avoid the formation or spread of mists in the air.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** For optimum shelf life product should be stored in original containers at 2-8 deg C  
**Suitable packaging:** Must only be kept in original packaging.

### 7.3. Specific end use(s)

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

**ETHYL-2-CYANOACRYLATE**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	-	1.5 mg/m <sup>3</sup>	-	-

### DNEL/PNEC Values

**DNEL / PNEC** No data available.

### 8.2. Exposure controls

**Engineering measures:** Ensure there is exhaust ventilation of the area.

**Respiratory protection:** Not applicable.

**Hand protection:** Polyethylene or polypropylene gloves are recommended when using large volumes. Do not use PVC, Rubber, Nylon or Cotton gloves.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

## Section 9: Physical and chemical properties

[cont...]

# SAFETY DATA SHEET

ADESCO AD150 CYANO 50G

Page: 5

## 9.1. Information on basic physical and chemical properties

**State:** Liquid  
**Colour:** Colourless  
**Odour:** Sharp characteristic odour.  
**Solubility in water:** Insoluble  
**Also soluble in:** Acetone. (Completely soluble)  
**Boiling point/range°C:** 150  
**Vapour pressure:** 0.293 mmHg  
**Flash point°C:** 85  
**Relative density:** 1.04

## 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.  
Decomposition may occur on exposure to conditions or materials listed below.

### 10.4. Conditions to avoid

**Conditions to avoid:** Rapid exothermic polymerisation will occur in the presence of water, amines, alkalis and alcohols.

### 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong acids. Water.

### 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

#### Toxicity values:

Route	Species	Test	Value	Units
DERMAL	RBT	LD50	>2000	mg/kg
ORAL	RAT	LD50	>5000	mg/kg

[cont...]

**SAFETY DATA SHEET**  
ADESCO AD150 CYANO 50G

Page: 6

**Hazardous ingredients:**

**ETHYL-2-CYANOACRYLATE**

ORL	RAT	LD50	>5	ml/kg
-----	-----	------	----	-------

**Relevant hazards for substance:**

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
STOT-single exposure	INH	Hazardous: calculated

**Symptoms / routes of exposure**

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** Cyanoacrylate will bond to eye protein and will cause periods of weeping which will help to debond the adhesive. In a dry atmosphere, 50% RH, vapours may cause irritation and lachrymatory effect.

**Ingestion:** Cyanoacrylates are considered to have relatively low toxicity. Acute oral LD50 is >5000 mg/kg (rat). It is almost impossible to swallow as it rapidly polymerises in the mouth.

**Inhalation:** In dry atmospheres with <50% humidity, vapours may irritate the eyes and respiratory system. Prolonged exposure to high concentrations of vapours may lead to chronic effects in sensitive individuals.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

**Section 12: Ecological information**

**12.1. Toxicity**

**Ecotoxicity values:** No data available.

**12.2. Persistence and degradability**

**Persistence and degradability:** Biodegradable.

**12.3. Bioaccumulative potential**

**Bioaccumulative potential:** No data available.

**12.4. Mobility in soil**

**Mobility:** No data available.

**12.5. Results of PBT and vPvB assessment**

**PBT identification:** This product is not identified as a PBT/vPvB substance.

**12.6. Other adverse effects**

**Other adverse effects:** No data available.

[cont...]

# SAFETY DATA SHEET

ADESCO AD150 CYANO 50G

Page: 7

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal operations:** Dispose of in accordance with local and national regulations. Polymerise by adding slowly to water (10:1) and dispose of as water insoluble, non-toxic solid chemical in authorised landfill or incinerate under controlled conditions.

**Disposal of packaging:** Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

**Transport class:** This product does not require a classification for transport.

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

### 15.2. Chemical Safety Assessment

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

\* indicates text in the SDS which has changed since the last revision.

**Phrases used in s.2 and s.3:** EUH202: Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H335: May cause respiratory irritation.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.