OR-GXC422942-A1-B

La legrand[®] designed to be better.

Mighty Mo GX Pre-configured Network Cabinet

OR-GXC422942-A1-B



42U x 29.5"W x 42"D, with Side Panels and Casters, 80.2" overall height, Basic Black

features & benefits

- Fully adjustable EIA mounting rails: Provides infinite adjustments.
- **3,000 lb. static frame load capacity:** Able to support the most high density switches.
- •Two-piece Side Panels: Easy handling.
- 180 degree door swing: Full equipment access.
- Top and bottom cable access: Additional flexibility.

Pre-Configured cabinet includes:

- A set of Side Panels (for stand alone or to create ends of row)
- Frame levelers and casters
- Two pairs of RU labeled equipment mounting rails with 12-24" tapped holes
- Full mesh front door
- Split mesh rear door
- Vetical PDU Mount/Lacing Bar
- Solid top panel with 2 4" diameter gland grommets
- #12-24 panel mounting screws (package of 50)
- Includes ganging hardware for connecting frames

(Consult sales to configure a cabinet to your specifications)

specifications

General Info

Type: Cabinets Component Type: Pre-Configured Cabinets

Construction Information

Component1: Frame Component2: Mounting Rails Component3: Doors Finish Plating1: Black Finish Plating2: Black Finish Plating3: Black Material1: 16 GA (.060") steel Material2: 14 GA (.075") steel Material3: 16 GA (.060") steel

Dimensions

Capacity Weight U S: 3,000 lb static frame load capacity Depth U S: 42" Width U S: 24" Rack Units: 42 Height: 80.15"