Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



8764 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information please call

1-800-Belden1



General Description:

22 AWG solid conductors, PVC insulation, tinned copper, twisted pairs, individually shielded w/Beldfoil® (100% coverage), 22 AWG solid TC drain wire, overall PVC jacket.

Physical Characteristics (Overall) Conductor AWG: # Pairs AWG Stranding Conductor Material 22 Solid TC - Tinned Copper **Total Number of Conductors:** 18 Insulation Insulation Material: **Insulation Material** Wall Thickness (in.) PVC - Polyvinyl Chloride | .013 **Inner Shield** Inner Shield Material: Inner Shield Trade Name Type Inner Shield Material Coverage (%) Beldfoil® (Z-Fold®) Tape | Aluminum Foil-Polyester Tape | 100 Inner Shield Drain Wire AWG: AWG 22 Inner Shield Drain Wire Stranding: Solid Inner Shield Drain Wire Conductor Material: TC - Tinned Copper **Outer Jacket** Outer Jacket Material: Outer Jacket Material Nom. Wall Thickness (in.) PVC - Polyvinyl Chloride | .040 **Overall Cable Overall Nominal Diameter:** 0.425 in Pair Pair Color Code Chart: Number Color Black & Red Black & White Black & Green Black & Blue Black & Yellow Black & Brown Black & Orange

Mechanical Characteristics (Overall)

Red & White Red & Green

Operating Temperature Range:	-20°C To +80°C
UL Temperature Rating:	80°C (UL AWM Style 2464)
Bulk Cable Weight:	112 lbs/1000 ft.
Max. Recommended Pulling Tension:	262 lbs.
Min. Bend Radius/Minor Axis:	4.250 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

Page 1 of 2 01-09-2015

Detailed Specifications & Technical Data





8764 Multi-Conductor - Audio, Control and Instrumentation Cable

N	IEC/(UL) Specification:	CMG, MPG		
C	EC/C(UL) Specification:	CMG, MPG		
A	WM Specification:	UL Style 2464 (300 V 80°C)		
E	U Directive 2011/65/EU (ROHS II):	Yes		
E	U CE Mark:	Yes		
E	U Directive 2000/53/EC (ELV):	Yes		
E	U Directive 2002/95/EC (RoHS):	Yes		
E	U RoHS Compliance Date (mm/dd/yyyy):	04/01/2005		
E	U Directive 2002/96/EC (WEEE):	Yes		
E	U Directive 2003/11/EC (BFR):	Yes		
C	A Prop 65 (CJ for Wire & Cable):	Yes		
N	III Order #39 (China RoHS):	Yes		
Flame	e Test			
U	IL Flame Test:	UL1685 FT4 Loading		
С	SA Flame Test:	FT4		
Plenu	ım/Non-Plenum			
Р	lenum (Y/N):	No		

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/ft) .19

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 12 Ohm/1000 ft

Max. Operating Voltage - UL:

Voltage 300 V RMS

Max. Recommended Current:

Current 1.5 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8764 0601000	1,000 FT	120.000 LB	CHROME	С	9 #22 SHPR PVC

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 10-05-2012

© 2015 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product

product.
Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

Page 2 of 2