



SNA Terminal Blocks

T&B Catalog Number:

011566323

UPC Number:

66201995750

Status:

Active

Description:

Gray, fuse holder block with 8 mm spacing, 10 Amp rated UL current with screw clamp connection that accepts 22-12 AWG UL wire range

Features

Self-locking clamp design prevents screw loosening

Quick fuse installation and replacement

Touch-safe IP20 protection

High quality steel offers a very high over-torque resistance

Compensates for the flattening of copper under contact pressure

Clamp is protected from harsh environments by a zinc bichromate surface treatment

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style Fuse Holder

Color Gray

Mounting DIN 1-3

Series M 4/8.SFL

Connection Technology Screw Clamp

UL Wire Range (AWG) 22-12

Rated IEC Wire Range (Solid) (mm²) 4

Rated CSA Wire Size (AWG) 12

Dimension Information

L x W x H (mm) 62 x 8 x 53.5

Spacing (mm) 8

L x W x H (in) 2.44 x 0.315 x 2.10

Spacing (inches) 0.315

Specifications

UL Current (Amps) 10

UL Voltage (VAC) 600

Rated UL Wire Size (AWG) 12

IEC Voltage (VAC) 400

IEC Current (Amps) 6.3

CSA Voltage (VAC) 250

CSA Current (Amps) 10

Packaging

T&B Order Multiple 50

T&B Inner Pack 50

Package in Units 450

T&B Sold in UOM Each

T&B Weight Per UOM 0.03 lbs. Each

Certifications

Approvals

UL, IEC, CSA

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com