



## SNA Terminal Blocks

### T&B Catalog Number:

029001125  
66201996988  
Active

**UPC Number:**

**Status:**

**Description:**

Gray, feed through terminal block with 5 mm spacing, 15 Amp rated UL current with spring clamp connection that accepts 26-12 AWG UL wire range

### Features

Top entry wire connection

Touch-safe IP20 protection

### Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

### General

Style	Feed Through
Color	Gray
Mounting	DIN 3
Series	D 2,5/5.4L
Connection Technology	Spring Clamp
UL Wire Range (AWG)	26-12
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	2.5
Rated CSA Wire Size (AWG)	12

### Dimension Information

L x W x H (mm)	80 x 5 x 45.5
Spacing (mm)	5
L x W x H (in)	3.15 x .198 x 1.79
Spacing (inches)	0.197

### Specifications

UL Current (Amps)	15
UL Voltage (VAC)	600
Rated UL Wire Size (AWG)	12
IEC Voltage (VAC)	800
IEC Current (Amps)	24
CSA Voltage (VAC)	600
CSA Current (Amps)	15

### Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	1250
T&B Sold in UOM	Each
T&B Weight Per UOM	2 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289

