

## Uniprise Solutions

760193250 | WBE-FXS-KIT-EXPRESS-SHINGLE-2-PORT-1.024

Split Shingle for Wall Mount Building Entrance, 2 port, 1.024 in

### Construction Materials

Material Type Steel

### Dimensions

Depth 6.4 mm | 0.3 in  
Height 76.20 mm | 3.00 in  
Width 203.20 mm | 8.00 in

### Environmental Specifications

Environmental Space Indoor

### General Specifications

Product Type Shingle  
Application Accepts cable with 0.708–1.024 in OD  
Color Gray  
Package Quantity 1

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

