

**Broadband Solutions****7764604 | F11SSVR****75 Ohm Coaxial Drop Cable, Series 11, NEC Riser, black flame retardant PVC jacket**

Construction Materials

Jacket Material	Fire retardant PVC
Center Conductor Material	Copper-clad steel
Dielectric Material	Foam PE
Inner Shield (Braid) Coverage	60 %
Inner Shield (Braid) Gauge	34 AWG
Inner Shield (Braid) Material	Aluminum
Inner Shield (Tape) Material	Aluminum/Polymer/Aluminum (APA) bonded
Outer Shield (Braid) Coverage	40 %
Outer Shield (Braid) Gauge	34 AWG
Outer Shield (Braid) Material	Aluminum
Outer Shield (Tape) Material	Aluminum/Polymer/Aluminum (APA)

Dimensions

Diameter Over Center Conductor, nominal	1.626 mm		0.064 in
Diameter Over Dielectric, nominal	7.112 mm		0.280 in
Diameter Over Inner Shield (Tape), nominal	7.290 mm		0.287 in
Diameter Over Jacket, nominal	10.338 mm		0.407 in
Jacket Thickness, nominal	0.9398 mm		0.0370 in
Shipping Weight	75.00 lb/kft		

Electrical Specifications

dc Resistance, Inner Conductor, nominal	12.50 ohms/kft
dc Resistance, Outer Conductor, nominal	3.70 ohms/kft
dc Resistance, Loop, nominal	16.20 ohms/kft
dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)
Capacitance	53.1 pF/m 16.2 pF/ft
Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±3 ohm
Nominal Velocity of Propagation (NVP)	85 %

Environmental Specifications

Environmental Space	Riser
Flame Test Listing	CATVR NEC Article 820

General Specifications

Cable Type	Series 11
Packaging Type	Reel
Shield Construction Type	Quad shield
Center Conductor Gauge	14 AWG
Center Conductor Type	Solid

7764604 | F11SSVR

Jacket Color	Black
Jacket Marking	Feet
Warranty	One year

Electrical Performance

Frequency	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5 MHz	1.25	0.38
55 MHz	3.15	0.96
83 MHz	3.87	1.18
187 MHz	5.74	1.75
211 MHz	6.23	1.90
250 MHz	6.72	2.05
300 MHz	7.38	2.25
350 MHz	7.94	2.42
400 MHz	8.53	2.60
450 MHz	9.02	2.75
500 MHz	9.51	2.90
550 MHz	9.97	3.04
600 MHz	10.43	3.18
750 MHz	11.97	3.65
865 MHz	13.05	3.98
1000 MHz	14.27	4.35

* Attenuation listed represents maximum values at standard condition of 20 °C (68 °F)

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system